

Maestro Wireless® product reference guide

What can you do with Maestro Wireless?



Add Convenience

- Control lights from anywhere in a room—or outside the home—with a Pico® wireless control
- Automate lights with an occupancy sensor to turn on as you enter a space and off again when you leave



Create Ambiance

- Adjust dimmers and lamp dimmers with Pico wireless controls to set the right light level for any activity
- Choose a tabletop lamp dimmer for local or wireless control, or choose the plug-in dimming module, which hides under or behind furniture, and is controlled with a Pico



Enhance Security

- Use a Pico wireless control to turn lights on from your car so you can walk into a well-lit home
- Add a switch where one is needed, rather than crossing a room in the dark—simply mount a Pico wireless control to the wall










Save Energy

- Turn lights off in unoccupied spaces with an occupancy sensor, or remotely as you leave your home with a Pico wireless control
- Turn off appliances in standby mode (such as printers, computers and charging stations) with the plug-in appliance module
- Dim lights to reduce energy usage or use a daylight sensor to automatically adjust light levels based on available daylight


Part numbers & pricing

Maestro Wireless® load controls

	Lutron P/N	Description	Features	Colors	List Price**
	MRF2-600M-	Maestro Wireless dimmer	Single-pole/multi-location dimmer 120V, 600W incandescent/halogen	All Satin and Gloss colors	\$ 88.00
	MRF2-6MLV-		Single-pole/multi-location dimmer 120 V, 600 W incandescent/halogen, MLV		\$ 100.00
	MRF2-10D-120-		Single-pole/multi-location dimmer 120V, 1000W incandescent/halogen, MLV voltage		\$ 130.00
	MRF2-6ND-120-		Single-pole/multi-location neutral wire dimmer 120 V, 600 W incandescent/halogen, MLV		\$ 130.00
	MA-R-	Maestro companion dimmer	Multi-location companion dimmer 120 V, provides multi-location dimming for up to 9 additional locations		\$ 27.50
	MRF2-8S-DV-	Maestro Wireless switch	Single-pole/multi-location dual volt no-neutral switch, 120V/277 V, 8A light, inc./halogen, MLV, ELV, non-dim fluorescent ballasts		\$ 150.00
	MRF2-6ANS-		Single-pole/multi-location switch 120 V, 6 A light or 3 A fan, incandescent, halogen, MLV, ELV, non-dim fluorescent ballasts, and general purpose fans	\$ 88.00	
	MRF2-6ANS-277-		Single-pole/multi-location switch 277 V, 6 A light, MLV, ELV, non-dim fluorescent ballasts	\$ 170.00	
	MA-AS-	Maestro companion switch	Multi-location companion switch 120 V, provides multi-location switching for up to 9 additional locations		\$ 35.50
	MA-AS-277-		Multi-location companion switch 277 V, provides multi-location switching for up to 9 additional locations	\$ 44.00	
	MRF2-3LD-	Maestro Wireless plug-in lamp dimmer	300W, incandescent/halogen for table or floor lamps	WH and BL only	\$ 130.00
	MRF2-3PD-1-	Maestro Wireless plug-in dimming module	Plug-in dimming/switching module; 300 W, inc./halogen for table or floor lamps, 1 receptacle		\$ 99.00
	MRF2-3PD-3-		Plug-in dimming/switching module; 300 W, inc./halogen for table or floor lamps, 3 receptacles	\$ 99.00	
	MRF2-15APS-1-	Maestro Wireless plug-in appliance module	Plug-in general purpose switch; 15 A, 1 receptacle		\$ 99.00
	MRF2-15APS-3-		Plug-in general purpose switch; 15 A, 3 receptacle	\$ 99.00	









Colors and finishes

Satin Colors®














 hot (HT)	 biscuit (BI)
 merlot (MR)	 snow (SW)
 plum (PL)	 palladium (PD)
 turquoise (TQ)	 midnight (MN)
 sea glass (SG)	 sienna (SI)
 taupe (TP)	 terracotta (TC)
 eggshell (ES)	 greenbriar (GB)

 bluestone (BG)
 mocha stone (MS)
 goldstone (GS)
 desert stone (DS)
 stone (ST)
 limestone (LS)

Gloss colors

 white (WH)	 brown (BR)
 ivory (IV)	 black (BL)
 almond (AL)	 white/gray (WG) pico wireless control only
 light almond (LA)	
 gray (GR)	

Radio Powr Savr™ wireless sensors & Pico® wireless controls

Lutron P/N	Description	Features	Colors	List Price**
 LRF2-OCR2B-P-WH*	Radio Powr Savr wireless sensor	360° ceiling-mount occupancy/vacancy sensor, auto-on/auto-off or manual on/auto-off, 3.572" diameter	WH only	\$ 85.00
 LRF2-OCRB-P-*		360° ceiling-mount occupancy/vacancy sensor, auto-on/auto-off or manual on/auto-off, 4" diameter	WH, LA and BL only	\$ 130.00
 LRF2-OWLB-P-WH*		180° wall-mount occupancy/vacancy sensor, auto-on/auto-off or manual on/auto-off	WH only	\$ 130.00
 LRF2-OKLB-P-WH*		90° corner-mount occupancy/vacancy sensor, auto-on/auto-off or manual on/auto-off		\$ 130.00
 LRF2-OHLB-P-WH*		Hallway occupancy/vacancy sensor, auto-on/auto-off or manual on/auto-off		\$ 130.00
 LRF2-DCRB-WH		ceiling-mount daylight sensor		\$ 120.00
 MRF2-3BRL-L-	Pico wireless control	5-button with on/off, raise/lower and favorite	All gloss colors and white/gray (WG)	\$ 56.00
 MRF2-2BRL-L-		4-button with on/off and raise/lower		\$ 56.00
 MRF2-3B-L-		3-button with on/off and favorite		\$ 56.00
 MRF2-2B-L-		2-button with on/off		\$ 56.00
 L-PED1-	Pedestal stand	Single table stand for Pico wireless control	WH and BL only	\$ 60.00
 L-PED2-		Double table stand for Pico wireless control		\$ 80.00
 CW-1-	Claro wallplate	1-gang opening	All Satin and Gloss colors	\$ 4.90

Packages

Lutron P/N	Description	Features	Colors	List Price**
MRF2-WHK-	Welcome Home package	(1) MRF2-600M-, (1) MRF2-6ANS-, (1) MRF2-3B-L-, and (2) CW-1-	WH and LA only	\$ 242.00
MRF2-600MTHW-	Dimmer and Pico package	(1) MRF2-600M-, (1) MRF2-3BRL-L-, and (1) CW-1-	WH and LA only	\$ 130.00

* Vacancy models available to meet residential California Title 24 section 119(j) requirements—all occupancy/vacancy sensors meet commercial requirements

** List price indicated for gloss colored products

Maestro Wireless® product reference guide

Load controls

Load controls work with Pico wireless controls, occupancy sensors, and/or daylight sensors. Limit 10 total devices.



Dimmer & switch

Width: 2.94" (75mm)
Height: 4.69" (119mm)



Lamp dimmer

Width: 2.45" (62mm)
Height: 3.23" (82mm)
Cord: 6' (1.83m)



Plug-in modules

lamp dimmer or appliance
switching versions
Width: 2.25" (57mm)
Height: 3.25" (83mm)
Socket Cord: 5" (127mm)
Plug Cord: 2' (0.6m)

Pico® wireless controls

Add up to 9 Pico controls to a single load control. Use a single Pico to control up to 9 load controls. Limit 10 total devices.



on/off,
raise/lower,
& favorite



on/off &
raise/lower



on/off
& favorite



on/off

Pico wireless control

Width: 1.28" (33mm)
Height: 2.60" (66mm)
Range: up to 100 ft.

Accessories



Wallmount
wallplate sold
separately



Car visor clip
included



Pedestal—single or double
sold separately

Radio Powr Savr™ wireless sensors

Each sensor works with up to 9 load controls—limit 3 occupancy sensors and 1 daylight sensor per single load control. Limit 10 total devices.



Ceiling-mount occupancy/vacancy* sensor

Diameter: 3.572" (90.73mm)
Depth: 1.30" (33mm)
Range: 60 ft. open air,
30 ft. through walls



Wall/hall/corner occupancy/vacancy* sensor

Width: 1.8" (46mm)
Height: 4.35" (110mm)
Depth: 1.35" (34mm)
Range: 60 ft. open air,
30 ft. through walls



Daylight sensor

Diameter: 1.60" (41mm)
Depth: 0.70" (17mm)
Range: 60 ft. open air,
30 ft. through walls

*vacancy only sensors available
to meet California Title 24
Section 119 (J) requirements