



Actual

Catalog Number: K650SOP
Product ID: 7TAA122240R0001
UPC Number: 78378665206
EAN Number: 05415022249507
Status: Active

15/25kV 600 Series Deadbreak Insulated Parking Bushing

North American Specifications (UNSPSC)

UNSPSC	26121630 Cable accessories
IGCC	1779 Cable accessories
Brand Name	Elastimold
Type	Parking Bushing
Special Features	Fully rated 15/25kV, 600 Amp Deadbreak Insulated Parking Bushing. Allows visible external separation, isolation, and dead-ending. Stainless Steel Bracket. Hot Stick Operable.
Application	The Elastimold K650SOP Insulated Parking Bushing is equipped with a 15/25kV class, 600 Amp deadbreak interface, a parking stand and hot stick operable mounting hardware. The K650SOP is inserted into the parking stand with an insulated hot stick and secured in place. Mating Elastimold K655LR/K656LR deadbreak elbows can then be placed on the K650SOP to provide a fully shielded and fully submersible connection. Provisions for grounding the K650SOP mounting bracket are included.
Standard	ANSI/IEEE Standard 386
Size	3.00 inch (76.2 mm) Diameter, 3.88 inch (98.5 mm) Long, 4.82 inch (122.2 mm) Center of Bushing to top of EyeBolt
Material	EPDM Rubber

Packaging

Inner Quantity	1
Inner Dimensions (inches)	8.5x5.5x3.5
Outer Quantity	1
Outer Dimensions (inches)	43x45x20
Weight Uom	1.85 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com