

Dimmers



- Paddle turns on/off
- Slide up to brighten, down to dim
- **C•L®** dimmers provide reliable dimming of dimmable CFLs/LEDs, as well as halogens and incandescents
- **eco-dim®** model guarantees at least 15% energy savings compared to a standard switch†
- Locator light shines through paddle on select lighter colored models

- Incandescent/halogen dimmers**
- Dimmable CFL (screw-base) dimmers**
- Dimmable LED (screw-base) dimmers**

C•L dimmers

3-way/single-pole 120V 600W (INC) 150W (CFL or LED)	DVCL-153P- XX ¹
3-way/single-pole 120V 600W (INC) 150W (CFL or LED)	DVSCCL-153P- XX ²

Visit www.lutron.com/dimcflled for an approved list of dimmable CFL/LED bulbs, and how to calculate wattage when mixing lamp types.

XX¹: Gloss color codes, see pg. 82
XX²: Satin Colors® codes, see pg. 82
XX³: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA) (Wallplates not included. Order separately, see pg. 169)

Incandescent/halogen dimmers

Dimmers

Single-pole 120V 600W	DV-600P- XX ¹ DVSC-600P- XX ²
Single-pole 120V 1000W	DV-10P- XX ¹ DVSC-10P- XX ²
3-way 120V 600W	DV-603P- XX ¹ DVSC-603P- XX ²
3-way 120V 1000W	DV-103P- XX ¹ DVSC-103P- XX ²

eco-dim® dimmer†

3-way/single-pole 120V 600W	DV-603PG- XX ³
--------------------------------	----------------------------------

Magnetic low-voltage dimmers

Dimmers

Single-pole 120V 600VA (450W)	DVLV-600P- XX ¹ DVSCLV-600P- XX ²
Single-pole 120V 1000VA (800W)	DVLV-10P- XX ¹ DVSCLV-10P- XX ²
3-way 120V 600VA (450W)	DVLV-603P- XX ¹ DVSCLV-603P- XX ²
3-way 120V 1000VA (800W)	DVLV-103P- XX ¹ DVSCLV-103P- XX ²

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load. The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.

All models must be derated if ganged unless otherwise noted, see pg. 179.

†Maximum light output of 85% guarantees 15% energy savings over standard switches.