



Lighting Your Life Since 1970

Product Specifications - 12762WTPN

Job Name:	Job Type:
Quantity:	Comments:



12762WTPN
Rondo 2-Light Bath Vanity

Finish
Polished Nickel

Glass/Shade
White

Product Category
Bath Vanity

Lamping

Number of Bulbs	2
Light Type	Incandescent
Bulb Type	CA
Max Bulb Wattage	60
Max Fixture Wattage	120
Rated Life	±1,500 Hours
Rated Lumens	±1,344
Color Temp	±2,700 K
Bulb(s)	Not Included
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	No
Dimmable	Standard Dimmer

Measurements

Width	16.75"
Height	8.25"
Length	N/A
Extension	8"
Back Plate Width	6.50"
Back Plate Height	4.49"
HCO	6.13"
Min Overall Height	N/A
Max Overall Height	N/A
Hanging Weight	3.31 lbs
Height Adjustable	N/A
Slope	N/A
Chain Length	N/A
Wire Length	N/A
Canopy Width	
Canopy Height	
Canopy Length	N/A

Shipping

Carton Weight	3.31 lbs
Carton Width	9"
Carton Height	9"
Carton Length	19"
Carton Cubic Feet	0.82
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

Certification

Safety Rating	Damp
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No
Dark Sky	N/A

Other

UPC Code	783209075382
Shades Included	N/A
Crystals Included	N/A
Diffuser Included	Yes
Conversion Kit	N/A
Material	N/A

Equivalents

Incandescent Watts	N/A
Fluorescent Watts	N/A

Maxim Lighting International and all designs, logos and images © 2014 Maxim Lighting International. All Rights Reserved. Maxim Lighting International reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes.

Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.