

Installation Accessories

Handles



For Zone 1/21 applications



For use with Class I/II Division 2 or Zone 1/21 fittings

Angles



DXN accessories are not returnable.

Cable Range	Poly Handle w/Bushing*	NPT	Poly Handle w/NPT***
.31 - .51	22-1A013-20P+	1/2"	22-1A013-12***
.51 - .75	22-1A013-25P+	3/4"	22-1A013-34***
.67 - .98	22-1A013-32P+		

Nylon 30° Angle
22-1A027

+ ATEX rated for use in Zone 1/21, not listed for Class I or II, Division 2.
 *** For use in Class I or II, Division 2 or Zone 1/21 depending on fitting used. Fitting manufactured by others.

NPT Guidelines

Cable Range	NPT
.312 - .625	1/2"
.438 - .812	3/4"

NPT sizes are determined by the cable diameter and third party cord grip.

Wall Boxes



82.3 in³+



4.5 in³+



4.5 in³+



75.0 in³+

Cable Range	Poly 70 ⁺⁺ Wall Box	NPT	Poly 30 ^{**} Wall Box	Poly 30 ^{***} Wall Box	Poly 70 ^{****} Alum Wall Box
.393 - .551	22-1AB58	1/2"	22-1A023-12-T	22-1A023-12-B	22-1A058-12
		3/4"	22-1A023-34-T	22-1A023-34-B	22-1A058-34
		1"	-	-	22-1A058-1
		1 1/4"	-	-	22-1A058-114
		1 1/2"	-	-	22-1A058-112

+ Interior volume with receptacle installed.
 ++ Poly cord grip is located on the top of box. For bottom cord entry, rotate the box 180°.
 * NPT thread on top.
 ** NPT thread on bottom.
 *** NPT is drilled on top of aluminum box as standard. For NPT on side only, add an "L" suffix. To switch from top to bottom or left to right the box can be rotated 180°.

Accessory Spotlight

Receptacle Lockout Pin



A 5/16" lockout pin can be ordered to securely lockout receptacles that include the "padlockable pawl" option. Alternatively the user can utilize a lock with a 5/16" shank. Locks with smaller shanks will NOT securely lockout a receptacle pawl.

Miscellaneous Accessories



* Set of Two (2)



For Male Devices Only



Finger Drawplates	Protective Cap	Receptacle + Lockout Pin
61-1A346	22-1A426	LP-843

* Recommended for cord to cord assembly applications, for easier connector closure.
 + Requires Padlockable Pawl option (-843) on receptacle.

HP rated DXN20

DXN20 Horsepower Ratings

AMPS	VAC (Max) @ 60 Hz	Phases	HP Rating
20	120V	1Ø	1/2 hp
20	240V	3Ø	2 hp
20	480V	3Ø	5 hp
20	600V	3Ø	5 hp



• HP ratings are based on CSA certification

Order Example

A typical order should include an inlet part number, a receptacle part number **AND** the matching handles, angles or other required accessories.



Male Inlet with Handle (Plug)
 22-18043 + 22-1A013-20P



Female Receptacle with Wall Box
 22-14043 + 22-1A023-12-T