

DS60



DECONTACTOR™ – 60A

Switch Rated Plugs & Receptacles

Ratings

- Voltage**
600 VAC
- Switch Rating (AC Only)**
Branch Circuit & Motor Circuit Disconnect Switching
- Horsepower Ratings**

120V	10	2 hp
240V	10	3 hp
208V	30	7 1/2 hp
240V	30	7 1/2 hp
480V	30	20 hp
600V	30	25 hp
- Short Circuit Rating**
100kA Close & Withstand
Testing was performed with RK1 current limiting fuses sized at 400% of the highest full load motor ampacity associated with the devices hp rating.
- Environmental Ratings**
Type 3R, IP54/IP55*
* IP54 when the plug & receptacle are mated. IP55 on the receptacle alone when the lid is latched closed.
- Temperature Range**
Min -40°F/Max 140°F
See pg 220 for temps below -15°F.
- Wiring Capacity**
Min 10 AWG Max 2 AWG
Aux Contacts - Max 14 AWG
- Listings**
UL, CSA, IEC, CE*
* Contact Customer Service

Receptacle (female)



Don't forget to add installation accessories to your order

Inlet (male)



Voltage	Polarity	Part #	
		Poly	Metal
120/208V	3P+N+G	33-64167	37-64167
125V	1P+N+G	33-64075	37-64075
125/250V	2P+N+G	33-64076	37-64076
208V	2P+G	33-64162	37-64162
208V	3P+G	33-64163	37-64163
250V	2P+G	33-64072	37-64072
250V	3P+G	33-64073	37-64073
277V	1P+N+G	33-64045	37-64045
277/480V	3P+N+G	33-64047	37-64047
347/600V	3P+N+G	33-64147	37-64147
480V	2P+G	33-64042	37-64042
480V	3P+G	33-64043	37-64043
600V	2P+G	33-64142	37-64142
600V	3P+G	33-64143	37-64143

Voltage	Polarity	Part #	
		Poly	Metal
120/208V	3P+N+G	33-68167	37-68167
125V	1P+N+G	33-68075	37-68075
125/250V	2P+N+G	33-68076	37-68076
208V	2P+G	33-68162	37-68162
208V	3P+G	33-68163	37-68163
250V	2P+G	33-68072	37-68072
250V	3P+G	33-68073	37-68073
277V	1P+N+G	33-68045	37-68045
277/480V	3P+N+G	33-68047	37-68047
347/600V	3P+N+G	33-68147	37-68147
480V	2P+G	33-68042	37-68042
480V	3P+G	33-68043	37-68043
600V	2P+G	33-68142	37-68142
600V	3P+G	33-68143	37-68143

Other voltage configurations are available – contact customer service at 800.433.7642.

Main Options



Auxiliary/Pilot Contacts



Mushroom Pawl



Padlock Pawl



Closed Lid Configuration

Recommended for cord applications to keep lid tucked in to avoid damage.



See pgs 197-206 for detailed information on these options

Receptacle Options

Suffix

With 2 Auxiliary/Pilot Contacts	Recept # - 972
With 3 Auxiliary/Pilot Contacts	Recept # - 263*
Type 4X & closed lid configuration	Recept # - 4X
Straight Insertion	Recept # - A188
Self-Ejecting Connector Release	Recept # - 348-A188
Mushroom Pawl	Recept # - 375
Padlock Pawl	Recept # - 843
Padlockable Mushroom Pawl	Recept # - 375-843
Locking Mushroom Pawl	Recept # - 845
Metal Pawl (on poly receptacle)	Recept # - 824
Closed Lid Configuration	Recept # - NC
With Auxiliary Switch	Recept # - 270**

Notes: * Not available for metal devices, not UL/CSA listed
** Not UL/CSA listed

Inlet Options

Suffix

With 2 Auxiliary/Pilot Contacts	Inlet # - 972
With 3 Auxiliary/Pilot Contacts	Inlet # - 263*
Type 4X Watertightness	Inlet # - 4X
Self-Ejecting Plug Release	Inlet # - 338-A188
Straight Insertion	Inlet # - A188
With No Lockout Hole	Inlet # - A155
For Auxiliary Switch*	Inlet # - NNF

Notes: * Order inlet with P+N+G configuration and receptacle with P+G configuration

DS60 Order Example:

To order 2 auxiliary/pilot contacts on an inlet and receptacle add -972 to the part numbers.

DS60 Poly inlet 3P+G=33-68043-972

DS60 Poly receptacle 3P+G=33-64043-972

Appropriate accessory part numbers must also be included on the order.