

DS30



DECONTACTOR™ – 30A

Switch-Rated Plugs & Receptacles

Ratings

- Voltage**
600 VAC
- Switch-Rating (AC Only)**
Branch Circuit & Motor Circuit Disconnect Switching
- Horsepower Ratings**

120V	1Ø	1 1/2 hp
240V	1Ø	3 hp
208V	3Ø	5 hp
240V	3Ø	5 hp
480V	3Ø	15 hp
600V	3Ø	15 hp
- Short Circuit Rating**
100kA Close & Withstand
Testing was performed with RK1 current limiting fuses sized at 400% of the highest full load motor ampacity associated with the devices hp rating.
- Environmental Ratings**
Type 3R, IP54/IP55*
* IP54 when the plug & receptacle are mated. IP55 on the receptacle alone when the lid is latched closed.
- Temperature Range**
Min -40°F/Max 140°F
See pg 228 for temps below -15°F.
- Wiring Capacity**
Min 14 AWG Max 6 AWG
Aux Contacts - Max 14 AWG
- Listings**
UL, CSA, IEC, CE*
* Contact Customer Service

Receptacle (female)



Don't forget to add installation accessories to your order

For international configurations (CE) visit meltric.com/international-catalog or contact customer service at 800.433.7642.

Inlet (male)



Voltage	Polarity	Part # Poly
120V	1P+N+G	33-34165
120/208V	3P+N+G	33-34167
125V	1P+N+G	33-34075
125/250V	2P+N+G	33-34076
208V	2P+G	33-34162
208V	3P+G	33-34163
250V	2P+G	33-34072
250V	3P+G	33-34073
277V	1P+N+G	33-34045
277/480V	3P+N+G	33-34047
347/600V	3P+N+G	33-34147
480V	2P+G	33-34042
480V	3P+G	33-34043
600V	2P+G	33-34142
600V	3P+G	33-34143

Voltage	Polarity	Part # Poly
120V	1P+N+G	33-38165
120/208V	3P+N+G	33-38167
125V	1P+N+G	33-38075
125/250V	2P+N+G	33-38076
208V	2P+G	33-38162
208V	3P+G	33-38163
250V	2P+G	33-38072
250V	3P+G	33-38073
277V	1P+N+G	33-38045
277/480V	3P+N+G	33-38047
347/600V	3P+N+G	33-38147
480V	2P+G	33-38042
480V	3P+G	33-38043
600V	2P+G	33-38142
600V	3P+G	33-38143

Main Options

- Auxiliary/Pilot Contacts**
- Mushroom Pawl**
- Padlock Pawl**
- Closed Lid Configuration**
Recommended for cord applications to keep lid tucked in to avoid damage.

Receptacle Options

Suffix

With 2 Auxiliary/Pilot Contacts	Recept # - 972
With 3 Auxiliary/Pilot Contacts	Recept # - 973
With 4 Auxiliary/Pilot Contacts	Recept # - 974
Type 4X & closed lid configuration	Recept # - 4X
Straight Insertion	Recept # - 352
Self-Ejecting Connector Release	Recept # - 354
Mushroom Pawl	Recept # - 375
Padlock Pawl	Recept # - 843
Padlockable Mushroom Pawl	Recept # - 375-843
Locking Mushroom Pawl	Recept # - 845
Metal Pawl (on poly receptacle)	Recept # - 824
Closed Lid Configuration	Recept # - NC
With Auxiliary Switch	Recept # - 270*

Inlet Options

Suffix

With 2 Auxiliary/Pilot Contacts	Inlet # - 972
With 3 Auxiliary/Pilot Contacts	Inlet # - 973
With 4 Auxiliary/Pilot Contacts	Inlet # - 974
Type 4X Watertightness	Inlet # - 4X
Self-Ejecting Plug Release	Inlet # - 338
With No Lockout Hole	Inlet # - A155
For Auxiliary Switch*	Inlet # - NNF

Notes: * Order inlet with P+N+G configuration and receptacle with P+G configuration

DS30 Order Example:

To order 2 auxiliary contacts on an inlet and receptacle add **-972** to the part numbers.

DS30 Poly inlet 3P+G=33-38043-**972**

DS30 Poly receptacle 3P+G=33-34043-**972**

Appropriate accessory part numbers must also be included on the order.

Notes: * Not UL/CSA Listed.

See pgs 205-214 for detailed information on these options