

MIN Series Size I Cordsets

European Color Code ❖ PVC Cable ❖ 18 AWG 300V Plugs



MIN Series Size I Cordsets

Face View of Male	# of Poles	Color Code	Wire AWG Rating	Length	Female Plugs		Male Plugs
					Straight	Right Angle	Straight
	3	1-Black 2-Brown 3-Blue	18 300V 8A	1 M	MINC-3FPX-1M	MINC-3FPX-1M-R	MINC-3MPX-1M
2 M				MINC-3FPX-2M	MINC-3FPX-2M-R	MINC-3MPX-2M	
4 M				MINC-3FPX-4M	MINC-3FPX-4M-R	MINC-3MPX-4M	
6 M				MINC-3FPX-6M	MINC-3FPX-6M-R	MINC-3MPX-6M	
10 M				MINC-3FPX-10M	MINC-3FPX-10M-R	MINC-3MPX-10M	
	3	1-Green/Yellow 2-Brown 3-Blue	18 300V 10A	1 M	MINE-3FPX-1M	MINE-3FPX-1M-R	MINE-3MPX-1M
2 M				MINE-3FPX-2M	MINE-3FPX-2M-R	MINE-3MPX-2M	
4 M				MINE-3FPX-4M	MINE-3FPX-4M-R	MINE-3MPX-4M	
6 M				MINE-3FPX-6M	MINE-3FPX-6M-R	MINE-3MPX-6M	
10 M				MINE-3FPX-10M	MINE-3FPX-10M-R	MINE-3MPX-10M	
	4	1-Brown 2-White 3-Blue 4-Black	18 300V 5.5A	1 M	MINC-4FPX-1M	MINC-4FPX-1M-R	MINC-4MPX-1M
2 M				MINC-4FPX-2M	MINC-4FPX-2M-R	MINC-4MPX-2M	
4 M				MINC-4FPX-4M	MINC-4FPX-4M-R	MINC-4MPX-4M	
6 M				MINC-4FPX-6M	MINC-4FPX-6M-R	MINC-4MPX-6M	
10 M				MINC-4FPX-10M	MINC-4FPX-10M-R	MINC-4MPX-10M	
	5	1-Black 2-Blue 3-Green/Yellow 4-Brown 5-White	18 300V 5.5A	1 M	MINE-5FPX-1M	MINE-5FPX-1M-R	MINE-5MPX-1M
2 M				MINE-5FPX-2M	MINE-5FPX-2M-R	MINE-5MPX-2M	
4 M				MINE-5FPX-4M	MINE-5FPX-4M-R	MINE-5MPX-4M	
6 M				MINE-5FPX-6M	MINE-5FPX-6M-R	MINE-5MPX-6M	
10 M				MINE-5FPX-10M	MINE-5FPX-10M-R	MINE-5MPX-10M	
	6	1-Green 2-White 3-Blue 4-Gray 5-Yellow 6-Brown	18 300V 5.5A	1 M	MINE-6FPX-1M	MINE-6FPX-1M-R	MINE-6MPX-1M
2 M				MINE-6FPX-2M	MINE-6FPX-2M-R	MINE-6MPX-2M	
4 M				MINE-6FPX-4M	MINE-6FPX-4M-R	MINE-6MPX-4M	
6 M				MINE-6FPX-6M	MINE-6FPX-6M-R	MINE-6MPX-6M	
10 M				MINE-6FPX-10M	MINE-6FPX-10M-R	MINE-6MPX-10M	

For Stainless Steel or Nylon coupling nut on straight female cordsets, add a "-SS" suffix for Stainless or "-N" for Nylon (e.g. MINE-3FPX-2M becomes MINE-3FPX-2M-SS). Please consult the factory for stainless steel or nylon right angle cordsets. Nylon is not available for male plugs. Please consult the factory for right angle male plugs.

Specifications:

Body: Oil Resistant Yellow PVC
 Contacts: Copper Alloy with Gold Plating
 Coupling Nut: Clear Anodized Aluminum
 Cable: Oil Resistant Yellow PVC Jacket,
 Rated at 300V, 105°C, Non-Wicking,
 Non-Hygroscopic, AWM Style 2661
 or SJTOOW
 Conductors: 18 AWG Bare Copper, PVC Insulated
 Temperature: -40°C to +105°C (-40°F to +221°F)
 Protection: IP 67
 Approvals: U.S.: UL Recognized
 Canada: C-UL Recognized

