



Ethernet Series Etherlink RJ45 Cordsets

8 Conductor Ethernet Series RJ45 Cordsets, 24AWG



RJ45 Cordsets | 42 VDC, 1.5 amps | IP67 Rating


Ethernet Series L

# of Poles	Front View	Wire AWG Rating	Features	Shield Type	RJ45 Male to Male Plug	RJ45 Male to Male Plug with Strain Relief
8	<p>RJ45</p>	24 AWG 42 VDC 1.5 A	PVC	N/A	RJ45-*	RJ45-8MMP-**
			PVC Foil Shield	Shield not Terminated	RJ45S-*	RJ45S-8MMP-**
			PUR	N/A	RJ45P-**	RJ45P-8MMP-**
			PUR Foil & Braided Shield	Shield not Terminated	RJ45PB-**	RJ45PB-8MMP-**
				Shield to RJ45 Connectors	RJ45SP-**	RJ45SP-8MMP-**
			TPE Foil & Braided Shield	Shield not Terminated	RJ45WB-**	RJ45WB-8MMP-**
				Shield to RJ45 Connectors	RJ45SW-**	RJ45SW-8MMP-**


* Lengths in feet. Standard cable lengths are 1, 3, 7, 10, 15, 20, 25 & 50 feet. Consult factory for other lengths.

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

***Cable Specifications on Page L-22 do not apply to these cables.



RJ45 Male to Male Plug



RJ45 Male to Male Plug with Strain Relief