

Accessories and Replacement Parts

Pin & Sleeve Wiring Devices 20 Amp - 100 Amp

Back Box ordering information



DESCRIPTION	METALLIC CATALOG NO.	NPT HUB	ANGLE	NON-METALLIC CATALOG NO.	NPT HUB*	ANGLE
20/30A Inlet & Receptacle	2030BBW	1"	30°	2030BBW-P	1"	15°
60A Receptacle	60BBW-1	1 1/4"	15°	60BBW-P	1 1/4"	15°
60A Inlet	60BBW	2"+	15°	N/A	N/A	N/A
100A Inlet & Receptacle	100BBW	2"+	15°	N/A	N/A	N/A

* HUB not included, Rough-in hole provided.

+ Provided with 1 1/2" reducer.

Protective Cap ordering information



AMP	# OF WIRES	DIMENSIONS (IN INCHES)	CATALOG NO.
20	3	2.76 x 1.61	ME 320CAP
20	4	3.11 x 1.61	ME 420CAP
20	5	3.39 x 1.65	ME 520CAP
30	3, 4	3.58 x 2.01	ME 3430CAP
30	5	3.90 x 2.05	ME 530CAP
60	3, 4, 5	4.25 x 2.87	ME 60CAP
100	3, 4, 5	4.69 x 3.11	ME 100CAP

Plug guard



Lockout / Tagout device for use on any IEC 60309-2 Pin & Sleeve Plug or Inlet.

Catalog No. **MEPG1**

Replacement Switches for Motor Disconnect Switches

FOR MODELS WITH MAX HP	CATALOG NO.
5 hp	ME 20XMS1-M2
10 hp	ME 32XMS1-M2
15 hp	ME 30XMS1-M2
20 hp	ME 40XMS2-M2
40 hp	ME 80XMS2-M2
50 hp	ME 100XMS2-M2

Replacement Covers for Motor Disconnect Switches

ENCLOSURE TYPE	CATALOG NO.
MS1A	ME MS1-RC
MS4A	ME MS4-RC
MS2A	ME MS2-RC
MS5A	ME MS5-RC

Field mountable Auxiliary Contact Blocks 1 N/O & 1 N/C for Motor Disconnect Switches

FOR MODELS WITH MAX HP	CATALOG NO.
5 hp & 10 hp	ME 20AUX
15 hp & 20 hp	ME 30AUX
40 hp & 50 hp	ME 80AUX

Field installable Hinge Kits for Motor Disconnect Switches

ENCLOSURE TYPE	CATALOG NO.
MS1A; MS4A	ME 106061
MS2A; MS5A	ME 19307000

Mounting Feet Kits for Motor Disconnect Switches

ENCLOSURE TYPE	CATALOG NO.
MS1A; MS4A	ME 236MIMF
MS2A; MS5A	ME MS2MF