

Description: 15, 20 amp din rail mount 120/240 VAC
Branch circuit rated 489 two pole. 10,000
AIC

Breaker Torque Value: 20 In-Lbs (2.3NM)
[Breaker and Busbar Torque Values](#)

All MidNite circuit breakers hold 100%
rated current independent of ambient
temperature.

Listed for US & Canada

Box Size 26mm wide

Weight 1 Lbs