




# Featured Models\*\*



= Accepts Class H Fuses (Fuses Not Included)

## Non Metallic – Non-Fusible Disconnects

Non-fusible disconnect pullers are removable or reinstallable in the OFF position for user safety during equipment maintenance.

UL	MODEL NUMBER	CIRCUIT PROTECTION	AMP	VOLTS	HORSE POWER RATING	WIRE RANGE*	CABINET SIZE*	UNIT WT.	STD. PKG.
Y	<b>P065P1</b>	NF65	60	240	10	D	5 X 7	2	6
Y	<b>P065NA1</b>	SWITCH ONLY	60	240	10	D	5 X 7	2	6
Y	<b>P065P</b>	NF65	60	240	10	D	6 X 8	2	6

## Non Metallic – Fusible Disconnects

Fusible disconnects are available in 30 and 60 Ampere models. Pullers are removable or reinstallable in the OFF position for user safety during equipment maintenance. The P065F UL listing includes the ability to field replace the 60 Ampere puller with a 30 Ampere puller (FR352) for installation flexibility. Listed for use as service entrance.

UL	MODEL NUMBER	CIRCUIT PROTECTION	AMP	VOLTS	HORSE POWER RATING	WIRE RANGE*	CABINET SIZE*	UNIT WT.	STD. PKG.
Y	<b>P035F</b>	FR39	30	240	3	D	6 X 8	2	6
Y	<b>P065F</b>	FR69	60	240	10	D	6 X 8	2	6

## Metallic – Non-Fusible Disconnects - Single & Three Phase

Non-fusible disconnect pullers are removable or reinstallable in the OFF position for user safety during equipment maintenance.

UL	MODEL NUMBER	PHASE	CIRCUIT PROTECTION	AMP	VOLTS	HORSE POWER RATING	WIRE RANGE*	CABINET SIZE*	UNIT WT.	STD. PKG.
Y	<b>U065P</b>	1	NF65	60	240	10	D	5 X 7	3	6
Y	<b>U0653P</b>	3	NF653	60	240	7.5-15	D	6 X 14	10	1
Y	<b>U065PD</b>	1	NF653	60	240	10	D	6 X 14	10	1

## Metallic – Fusible Disconnects - Single & Three Phase

Fusible disconnects are available in 30 and 60 Ampere models. Pullers are removable or reinstallable in the OFF position for user safety during equipment maintenance. Listed for use as service entrance.

UL	MODEL NUMBER	PHASE	CIRCUIT PROTECTION	AMP	VOLTS	HORSE POWER RATING	WIRE RANGE*	CABINET SIZE*	UNIT WT.	STD. PKG.
Y	<b>U035F2</b>	1	FR35R	30	240	3	D	5 X 9	4	6
Y	<b>U065F1</b>	1	FR65	60	240	10	D	5 X 9	4	6
Y	<b>U0353F</b>	3	FH393	30	240	3-7.5	D	6 X 14	10	1
Y	<b>U0653F</b>	3	FH693	60	240	7.5-15	D	6 X 14	10	1

\* See back page for details

Data Subject To Change Without Notice

\*\* Additional Basic And Custom Models Available, Consult Manufacturing Representative For Further Details