

SITOP MODULAR 24 V/40 A  
 SITOP modular 40 A stabilized power supply input: 400-500 V 3AC  
 output: 24 V DC/40 A



Input	
Input	3-phase AC
Rated voltage value $V_{in}$ rated	400 ... 500 V
Voltage range AC	320 ... 550 V
<ul style="list-style-type: none"> <li>Note</li> </ul>	Starting from $V_{in} > 340$ V
Wide-range input	Yes
Overvoltage resistance	$2.3 \times V_{in}$ rated, 1.3 ms
Mains buffering at $I_{out}$ rated, min.	6 ms; at $V_{in} = 400$ V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 ... 63 Hz
Input current	
<ul style="list-style-type: none"> <li>at rated input voltage 400 V</li> </ul>	2.2 A
Switch-on current limiting (+25 °C), max.	70 A
$I^2t$ , max.	2.8 A <sup>2</sup> ·s
Built-in incoming fuse	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 10 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)

Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.2 %
Residual ripple peak-peak, max.	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV
Adjustment range	24 ... 28.8 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer; max. 960 W
Status display	Green LED for 24 V OK
Signaling	via signaling module (6EP1961-3BA10)
On/off behavior	No overshoot of Vout (soft start)
Startup delay, max.	2.5 s
Voltage increase time of the output voltage maximum	500 ms
Rated current value Iout rated	40 A
Current range	0 ... 40 A
• Note	+60 ... +70 °C: Derating 2%/K
Supplied active power typical	960 W
Short-term overload current	
• at short-circuit during operation typical	120 A
Duration of overloading capability for excess current	
• at short-circuit during operation	25 ms
Constant overload current	
• on short-circuiting during the start-up typical	46 A
Parallel switching for enhanced performance	Yes; switchable characteristic
Numbers of parallel switchable units for enhanced performance	2

Efficiency	
Efficiency at Vout rated, Iout rated, approx.	90 %
Power loss at Vout rated, Iout rated, approx.	106 W

Closed-loop control	
Dynamic mains compensation (Vin rated ±15 %), max.	1 %
Dynamic load smoothing (Iout: 50/100/50 %), Uout ± typ.	2 %
Load step setting time 50 to 100%, typ.	4 ms
Load step setting time 100 to 50%, typ.	4 ms
Setting time maximum	10 ms

Protection and monitoring	
Output overvoltage protection	< 35 V

Current limitation, typ.	46 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Alternatively, constant current characteristic approx. 46 A or latching shutdown
Enduring short circuit current RMS value	
• typical	46 A
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"

## Safety

Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current	
• maximum	3.5 mA
CE mark	Yes
UL/cUL (CSA) approval	UL-Listed (UL 508), File E197259, CSA (CSA C22.2 No. 14, CSA C22.2 No. 107.1)
Explosion protection	IECEX Ex nA nC IIC T3 Gc; ATEX (EX) II 3G Ex nA nC IIC T3 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T3
FM approval	-
CB approval	No
Marine approval	-
Degree of protection (EN 60529)	IP20

## EMC

Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2

## Operating data

Ambient temperature	
• during operation	0 ... 70 °C
— Note	with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation

## Mechanics

Connection technology	screw-type terminals
Connections	
• Supply input	L1, L2, L3, PE: 1 screw terminal each for 0.2 ... 4 mm <sup>2</sup> single-core/finely stranded
• Output	+, -: 2 screw terminals each for 0.33 ... 10 mm <sup>2</sup>
• Auxiliary	-

Width of the enclosure	240 mm
Height of the enclosure	125 mm
Depth of the enclosure	125 mm
Required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
Weight, approx.	3.2 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x15
Electrical accessories	Buffer module, signaling module
MTBF at 40 °C	485 437 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)