



200 AMP-7 TERMINAL-MEDIUM DUTY-LEVER BYPASS-RINGLESS-3Ø4W

AMP	SERVICE	CATALOG NUMBER	HUB	CONNECTORS		BY-PASS	DIMENSIONS			CONCENTRIC K.O.'S					
				LINE	LOAD		D"	W"	H"	1	2	3	4	5	6
200	OH/UG	U7423-RXL*	C.P.	#6-350 kcmil	#6-350 kcmil	LEVER	4 ⁷ / ₈	13	19	3	2 ¹ / ₂	3	3	1/4	1/4, 1/2
200	OH/UG	U4029-X-DPL**	C.P.	#6-350 kcmil	#6-350 kcmil	LEVER	4 ⁷ / ₈	13	19	3	2 ¹ / ₂	3	3	1/4	1/4, 1/2

HUBS: For proper hub selection see the hub suffix chart on the accessory page.

LEVER BYPASS: Lever operates bypass only.

200 AMP-5 & 7 TERMINAL-HEAVY DUTY-LEVER BYPASS-RINGLESS-3Ø3W & 3Ø4W

AMP	SVC.	NO. OF TERMS.	CATALOG NUMBER	HUB	CONNECTORS		BY-PASS	DIMENSIONS			CONCENTRIC K.O.'S					
					LINE	LOAD		D"	W"	H"	1	2	3	4	5	6
200	OH/UG	5	U9551-X-DPL**	C.P.	#6-350 kcmil	#6-350 kcmil	LEVER	4 ⁷ / ₈	13	19	3	2 ¹ / ₂	3	3	1/4	1/4, 1/2
200	OH	5	S3970-XL*** ^①	C.P.	3/8"-16 stud	3/8"-16 stud	LEVER	4 ⁷ / ₈	13	19	3	2 ¹ / ₂	3	3	1/4	1/4, 1/2
200	OH	7	U9700-RRL-BLG*	H.O.	#6-350 kcmil	#6-350 kcmil	LEVER	4 ⁷ / ₈	10	18 ¹ / ₂	3	2 ¹ / ₂	3	-	1/4, 1/2	3/4
200	OH	7	S8930-XL*** ^①	C.P.	3/8"-16 stud	3/8"-16 stud	LEVER	4 ⁷ / ₈	13	19	3	2 ¹ / ₂	3	3	1/4	1/4, 1/2

HUBS: For proper hub selection see the hub suffix chart on the accessory page.

LEVER BYPASS: Lever supplies clamping action and operates bypass device.

UL APPROVAL: S3970 & S8930 units are NOT UL Listed or approved.

^①For S3970 order connector kit K1350 for single #6-350 connector, order K1540 for single #4-600 or twin 1/0-250. For S8930, order connector kit K3082 for single #6-350 connector, order K3441 for single #4-600 or twin 1/0-250.

200 AMP-7 TERMINAL-MEDIUM DUTY-SIDE WIREWAY-LEVER BYPASS-RINGLESS-3Ø4W

AMP	SERVICE	CATALOG NUMBER	HUB	CONNECTORS		BY-PASS	DIMENSIONS			CONCENTRIC K.O.'S					
				LINE	LOAD		D"	W"	H"	1	2	3	4	5	6
200	UG	U3786-O-BLG*	BLANK	#6-350 kcmil	#6-350 kcmil	LEVER	6	18	19 ¹ / ₄	3	2 ¹ / ₂	-	4	1/4, 1/2	-

CONNECTORS: Extruded aluminum connectors are tin plated.

LEVER BYPASS: Lever operates bypass only.

*APS approved

**Conectiv approved

*** PEPCO approved

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements before ordering or installing equipment in this catalog.

CATALOG NO.	UPC	DESCRIPTION	PAGE
DISCONNECTS			
U3803	13903	30A Fusible ACD	5
U3806	13904	60A Fusible ACD	5
U3800	13902	60A Non Fusible ACD	5
U3822-20GR	28282	60A N-F ACD/ 20A GFCI	6
U4881-O	36949	Hot Tub Disc Brk Prov	6
U4881-O-50GB	26815	50A Hot Tub Disc	6
U4881-O-60GB	27930	60A Hot Tub Disc	6

SINGLE POSITION METERING

125-200 amp-4, 5 & 7 Terminal-Ringless-600 VAC

U7487-YL-TG-KK-BLG	24178	125A 4T RL OH	7
U7040-XL-TG-KK	14039	200A 4T RL OH	7
U7040-RL-KK-DPL	37108	200A 4T RL OH	7
S1619-XL	12073	200A 4T RL Stud OH	7
U3126-O-KK-BLG	24174	200A 4T RL SWY UG	8
U1980-O-KK-DPL	37109	200A 4T RL SWY UG	8
U2986-O-PEP	23936	200A 4T RL SWY Stud UG	8
U7423-RXL	14100	200A 7T RL MD LVR OU	9
U4029-X-DPL	37114	200A 7T RL MD LVR OU	9
U9551-X-DPL	37115	200A 5T RL HD LVR OU	9
S3970-XL	27377	200A 5T RL Stud HD LVR OH	9
U9700-RRL-BLG	24194	200A 7T RL HD LVR OH	9
S8930-XL	27376	200A 7T RL Stud HD LVR OH	9
U3786-O-BLG	24650	200A 7T RL SWY MD LVR UG	9

SINGLE POSITION METERING

320 - 480 amp-4, 5 & 7 Terminal-Ringless-600 VAC

U4433-X	26860	320A 4T RL SWY Stud LVT OU	10
U4980-X	27983	320A 4T RL SWY Stud HD LVR OU	10
U2120-X	13466	320A 7T RL SWY Stud HD LVR UG	10
U4168-X-K7-BLG	24475	320A 7T RL SWY HD LVR OU	10
U1779-R-K3-BLG	24594	320A 4T RL Stud HD LVR OH	10
U1729-X-DPL	37110	320A 4T RL HD LVR UG	10
U1797-O-K3L-K2L	30172	320A 4T RL SWY HD LVR UG	10
U4664-X-8522-DPL	47868	480A Cont/600 Max 4T OU	11
U4667-X-8043-DPL	47869	480A Cont/600 Max 7T OU	11

MULTIPLE METERING

100 - 200 amp/Position-4 & 5 Terminal- Horizontal Gangs-Ringless-600 VAC

U8032-XL-KK-BLG	24179	100A 4T RL 2P Ctr Wy	12
U8033-XL-KK-BLG	24180	100A 4T RL 3P Ctr Wy	12
U8034-XL-KK-BLG	24181	100A 4T RL 4P Ctr Wy	12
U8035-XL-KK-BLG	24182	100A 4T RL 5P Ctr Wy	12
U8036-XL-KK-BLG	24183	100A 4T RL 6P Ctr Wy	12
U8212-XL-KK-BLG	24184	100A 4T RL 2P End Wy	13
U8213-XL-KK-BLG	24185	100A 4T RL 3P End Wy	13
U8214-XL-KK-BLG	24186	100A 4T RL 4P End Wy	13
U8215-XL-KK-BLG	24187	100A 4T RL 5P End Wy	13
U8216-XL-KK-BLG	24188	100A 4T RL 6P End Wy	13
U1252-X-KK-K3-BLG	24169	200A 4T RL 2P Ctr Wy	14
U1252-X-KK-K3-DPL	37111	200A 4T RL 2P Ctr Wy	14
U1253-X-KK-K3-BLG	24170	200A 4T RL 3P Ctr Wy	14
U1254-X-KK-K3-BLG	24171	200A 4T RL 4P Ctr Wy	14
U1254-X-KK-K3-DPL	37112	200A 4T RL 4P Ctr Wy	14
U1255-X-KK-K3-BLG	24172	200A 4T RL 5P Ctr Wy	14
U1256-X-KK-K3-BLG	24173	200A 4T RL 6P Ctr Wy	14
U1256-X-KK-K4-DPL	37113	200A 4T RL 6P Ctr Wy	14

CT CABINETS & TRANS SOCKETS

363612-CT3R	19831	CT Enc Type3R Hinged Pdlk	15
484812-CT3R	20269	CT Enc Type3R Hinged Pdlk	15
U4051-O	25421	10X36X28 Trans Encl	15
S4244-X	28632	400A 13T RL 600V TS	15

CATALOG NO.	UPC	DESCRIPTION	PAGE
COMMERCIAL PEDESTALS & ACCESSORIES			
CP3B52119A22AOSP	N/A	200A RL HDLB	17
CP3B52110A22AOSL1	N/A	200A RL HDLB SL	17
CP-ABK5/8	16490	Anchor Bolt Kit	17
CP-16PDMNT-CALT	16485	Ped Mounting Base	17
K3865	11401	5th Term Assy RL	17
105J	10082	5th Term Assy RT	17
CP-TC7D	31795	7-day Time Clock Kit	17
CP-TC24H	31794	24-hour Time Clock Kit	17
CP-TCWIRE	31864	Wiring harness	17
CP-PE-HOA-3POS	47696	Photoelectric cell kit	17

MISCELLANEOUS

Milbank Accessories

Z703916-AC	24044	Conn 1P 3/0-800 kcmil	18
Z703917-AC	24724	Conn 2P 6-350 kcmil	18
Z703918-AC	24045	Conn 2P 4-350 kcmil	18
Z703919-AC	23511	Conn 2P 350 kcmil	18
Z703921-AC	23984	Conn 1P 3/0-800 kcmil	18
Z704693-AC	25111	Conn 2P 500 kcmil-2	18
Z704694-AC	24865	Conn 2P 4-500 kcmil	18
Z705420-AC	24046	Conn 4P 6-350 kcmil	18
Z705456-AC	24047	Conn 2P 6-350 kcmil	18
Z708145-AC	24048	Conn 3P 6-250 kcmil	18
6003	10761	Gray Plastic Closing Plate	19
6116	10763	Clear Plastic Closing Plate	19
5T8K2	10760	5th Term Assy 100/200A Sockets	19
A7514-17	11039	1 Inch Hub Unit	19
A7518	11044	2 1/2 Inch Hub Unit	19
A7551	11046	Std Closing Plate	19
A8110	11047	3 Inch Hub Unit	19
A8111	11048	3 1/2 Inch Hub Unit	19
A8112	11049	4 Inch Hub Unit	19
CP-21	11208	Metal Closing Plate	19
K1350	11329	Twin Lug Assy 350 kcmil 1Ø	19
K1539	11333	Single Lug Assy 350 kcmil 1Ø	19
K1540	11334	Single Lug Assy 600 kcmil 1Ø	19
K1541	11335	Twin Lug Assy 600 kcmil 1Ø	19
K3082	11366	Single Lug Assy 350 kcmil 3Ø	19
K3083	11367	Twin Lug Assy 600 kcmil 3Ø	19
K3441	11387	Single Lug Assy 600 kcmil 3Ø	19
K3442	11388	Twin Lug Assy 350 kcmil 3Ø	19
K5T	21256	5th Term Assy	19
S8324	12819	Hub Adapter Plate	19
S9064	12889	Large Closing Plate	19

Utility Matrix20

Other Milbank Products21

Conduit and Ampacity Information22

Energization of Electrical Equipment23