

GSC3R Screw Cover Wiring Trough

Type 3R

67
TYPE 3R
SCREW COVER
WIRING TROUGH

| Catalog Number | Product Family | UPC Number 7-84572- | Weight (lbs) | Carton Quantity | H x D x L | Number of Knockouts |
|------------------|----------------|---------------------|--------------|-----------------|-------------|---------------------|
| 4424-GSC3R-NK-NP | GS3R | 16176 | 8.5 | 4 | 4 x 4 x 24 | None |
| 4436-GSC3R | GS3R | 10648 | 12 | 4 | 4 x 4 x 36 | 5 |
| 4436-GSC3R-NK | GS3R | 10649 | 12 | 4 | 4 x 4 x 36 | None |
| 4436-GSC3R-NK-NP | GS3R | 16175 | 12 | 4 | 4 x 4 x 36 | None |
| 4448-GSC3R | GS3R | 10660 | 15.8 | 4 | 4 x 4 x 48 | 7 |
| 4448-GSC3R-NK | GS3R | 10661 | 15.8 | 4 | 4 x 4 x 48 | None |
| 4448-GSC3R-NK-NP | GS3R | 16174 | 15.8 | 4 | 4 x 4 x 48 | None |
| 4460-GSC3R | GS3R | 10666 | 19.5 | 4 | 4 x 4 x 60 | 9 |
| 4460-GSC3R-NK | GS3R | 10667 | 19.5 | 4 | 4 x 4 x 60 | None |
| 4460-GSC3R-NK-NP | GS3R | 16173 | 19.5 | 4 | 4 x 4 x 60 | None |
| 4472-GSC3R | GS3R | 10671 | 23.5 | 4 | 4 x 4 x 72 | 11 |
| 4472-GSC3R-NK | GS3R | 10672 | 23.5 | 4 | 4 x 4 x 72 | None |
| 4472-GSC3R-NK-NP | GS3R | 19304 | 23.5 | 4 | 4 x 4 x 72 | None |
| 4496-GSC3R | GS3R | 21984 | 31.1 | 2 | 4 x 4 x 96 | 15 |
| 44120-GSC3R | GS3R | 21985 | 38.7 | 2 | 4 x 4 x 120 | 19 |
| 6612-GSC3R | GS3R | 10774 | 7 | 2 | 6 x 6 x 12 | 3 |
| 6612-GSC3R-NK | GS3R | 10775 | 7 | 2 | 6 x 6 x 12 | None |
| 6612-GSC3R-NK-NP | GS3R | 17550 | 7 | 2 | 6 x 6 x 12 | None |
| 6618-GSC3R | GS3R | 10782 | 10 | 2 | 6 x 6 x 18 | 3 |
| 6618-GSC3R-NK | GS3R | 10783 | 10 | 2 | 6 x 6 x 18 | None |
| 6618-GSC3R-NK-NP | GS3R | 21096 | 10 | 2 | 6 x 6 x 18 | None |
| 6624-GSC3R | GS3R | 10788 | 12.5 | 2 | 6 x 6 x 24 | 3 |
| 6624-GSC3R-NK | GS3R | 10789 | 12.5 | 2 | 6 x 6 x 24 | None |
| 6624-GSC3R-NK-NP | GS3R | 16172 | 12.5 | 2 | 6 x 6 x 24 | None |
| 6636-GSC3R | GS3R | 10796 | 18 | 2 | 6 x 6 x 36 | 5 |
| 6636-GSC3R-NK | GS3R | 10797 | 18 | 2 | 6 x 6 x 36 | None |
| 6636-GSC3R-NK-NP | GS3R | 16171 | 18 | 2 | 6 x 6 x 36 | None |
| 6648-GSC3R | GS3R | 10815 | 24 | 2 | 6 x 6 x 48 | 7 |
| 6648-GSC3R-NK | GS3R | 10816 | 24 | 2 | 6 x 6 x 48 | None |
| 6648-GSC3R-NK-NP | GS3R | 16170 | 24 | 2 | 6 x 6 x 48 | None |
| 6660-GSC3R | GS3R | 10826 | 28.5 | 2 | 6 x 6 x 60 | 9 |
| 6660-GSC3R-NK | GS3R | 10827 | 28.5 | 2 | 6 x 6 x 60 | None |
| 6660-GSC3R-NK-NP | GS3R | 19303 | 28.5 | 2 | 6 x 6 x 60 | None |
| 6672-GSC3R | GS3R | 10830 | 34 | 2 | 6 x 6 x 72 | 11 |
| 6672-GSC3R-NK | GS3R | 10831 | 34 | 2 | 6 x 6 x 72 | None |
| 6672-GSC3R-NK-NP | GS3R | 19004 | 34 | 2 | 6 x 6 x 72 | None |
| 6696-GSC3R | GS3R | 10834 | 45 | 1 | 6 x 6 x 96 | 15 |
| 6696-GSC3R-NK | GS3R | 10835 | 45 | 1 | 6 x 6 x 96 | None |
| 6696-GSC3R-NK-NP | GS3R | 23847 | 45 | 1 | 6 x 6 x 96 | None |
| 66120-GSC3R | GS3R | 20971 | 55 | 1 | 6 x 6 x 120 | 19 |
| 66120-GSC3R-NK | GS3R | 26496 | 55 | 1 | 6 x 6 x 120 | None |
| 8812-GSC3R | GS3R | 10918 | 9 | 1 | 8 x 8 x 12 | 3 |

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements before ordering or installing equipment.

