



Nothing but **HEAVY DUTY.**

DESIGNED TO A HIGHER STANDARD

Milwaukee® offers a comprehensive line of Test & Measurement tools built specifically for you. Everything from our high contrast white on black displays, to our built in work light and voltage detection, to our rugged over molding is designed to make your job easier. Milwaukee® also offers the only rechargeable system for Test & Measurement tools, powered by our M12™ LITHIUM-ION battery. Built to last, Milwaukee® Test & Measurement tools are backed by the Milwaukee® 5 Year Warranty.



CLAMP-GUN™ M12™ Cordless Clamp Meter Kit for HVAC/R

2238-21 (Bare tool 2238-20)

Specifications:

Current Range	600A AC
Voltage Range	1,000V AC/DC
Safety Rating	CAT IV 600V / CAT III 1,000V
Contact Temperature Range	-40° F to 1,000° F (-40° C to 538° C)



Includes (1) M12™ LITHIUM-ION Battery Pack, 30-Minute Charger, Electrical Test Lead Set, Dual Banana Thermocouple, Carrying Case, Manual



SUB-SCANNER™ M12™ Cordless Detection Tool Kit

2290-21 (Bare tool 2290-20) (Combo Kit 2290-23)

Specifications:

Detects Rebar in Concrete	YES
Depth (Metal)	6"
Depth (Wood, Metal Stud)	1-1/2"
Stud Edges & Center	YES



Includes (1) M12™ LITHIUM-ION Battery Pack, 30-Minute Charger, Carrying Case, Manual



CLAMP-GUN™ M12™ Cordless Clamp Meter Kit

2239-21 (Bare tool 2239-20) (Combo Kit 2239-23)

Specifications:

Current Range	1,000A AC/DC
Voltage Range	1,000V AC/DC
Safety Rating	CAT IV 600V / CAT III 1,000V
TRMS	YES



Includes (1) M12™ LITHIUM-ION Battery Pack, 30-Minute Charger, Electrical Test Lead Set, Carrying Case, Manual



M12™ Fork Meter

2207-21 (Bare tool 2207-20)

Specifications:

Current Range	200A AC
Voltage Range	1,000V AC/DC
Safety Rating	CAT IV 600V / CAT III 1,000V
Fork Opening	0.63"
TRMS	YES



Includes (1) M12™ LITHIUM-ION Battery Pack, 30-Minute Charger, Electrical Test Lead Set, Carrying Case, Manual



LASER TEMP-GUN™ M12™ Cordless Thermometer Kit

2276-21 (Bare tool 2276-20) (Combo Kit 2276-23)

Specifications:

Temperature Range	-22° F to 1,472° F (-30° C to 800° C)
Basic Accuracy	1.50%
Distance to Spot	40 to 1
Contact Temperature Range	-40° F to 1,022° F (-40° C to 550° C)



Includes (1) M12™ LITHIUM-ION Battery Pack, 30-Minute Charger, K-Type Thermocouple, Carrying Case, Manual



Fork Meter

2205-20

Specifications:

Current Range	200A AC
Voltage Range	1,000V AC/DC
Lo-Z	YES
Safety Rating	CAT IV 600V / CAT III 1,000V
Fork Opening	0.63"
TRMS	YES



Includes Electrical Test Lead Set, (2) AA Batteries, Manual



LASER TEMP-GUN™ M12™ Cordless Thermometer Kit for HVAC/R

2277-21 (Bare tool 2277-20)

Specifications:

Humidity & Dew Point	YES
Temperature Range	-22° F to 1,472° F (-30° C to 800° C)
Basic Accuracy	1.50%
Distance to Spot	40 to 1
Contact Temperature Range	-40° F to 1,022° F (-40° C to 550° C)



Includes (1) M12™ LITHIUM-ION Battery Pack, 30-Minute Charger, K-Type Thermocouple, Carrying Case, Manual



Fork Meter for HVAC/R

2206-20

Specifications:

Current Range	200A AC
Voltage Range	1,000V AC/DC
Safety Rating	CAT IV 600V / CAT III 1,000V
Contact Temperature Range	-40° F to 752° F (-40° C to 400° C)
Fork Opening	0.63"
TRMS	YES



Includes Electrical Test Lead Set, Dual Banana Thermocouple, (2) AA Batteries, Manual

