

BRUSHLESS
MOTORSLONGER
MOTOR LIFEMORE
POWERMORE
RUN-TIME

LEARN MORE ▶

Nothing but **HEAVY DUTY.**
[Home](#) > [Products](#) > [Tools](#) > [Cordless Tools](#) > [Heated Gear](#) > M12™ Cordless High Visibility Heated Jacket Kit

M12™ Cordless High Visibility Heated Jacket Kit 2347

0.0 **Be the first to Write a Review**

The M12™ Cordless High Visibility Heated Jacket is ANSI Class III certified to meet or exceed jobsite and roadside construction standards to ensure user safety. The jacket utilizes multi layered fabric technology, a fleece inner liner and durable carbon fiber heating elements in the chest and upper back to actively warm the body and stimulate blood circulation to provide unmatched warmth and performance.

The 2346/2347 M12™ High Visibility Heated Jacket features three heat settings, for varying heat needs and is water and wind resistant for a variety of cold jobsite conditions. Hidden in a sleek back pocket, which can expand to hold an XC battery, the M12™ RED LITHIUM battery delivers superior runtime, with up to 6 hours of heat on a single charge. The jacket also features a zip-in removable hood for versatility on the jobsite and a hidden inside pocket to facilitate custom embroidery by construction companies or individual end users. Jackets available in sizes ranging from M - 4XL

Includes

- 2346 M12™ Cordless High Visibility Heated Jacket
- Removable Hood
- (1) RED LITHIUM™ Battery
- 30-minute Charger

FEATURES

- ANSI Class III Certified to Meet or Exceed Jobsite and Roadside Construction Standards
- Superior Run-Time: Up to 6 hours of continuous heat per battery charge
- Water and Wind Resistant
- Core Heat Zone Provides Heat to the Chest and Upper Back
- 3 Heat Settings Per Zone (High, Medium, Low)
- Easy Touch Heat Controller Located on Inside of Lapel
- Zip-in Removable Hood
- Hidden Inside Pocket to Facilitate Easy Custom Embroidery
- Expandable battery pouch for use with M12™ RED LITHIUM™ Compact or M12™ RED LITHIUM™ XC Battery Pack
- Compatible: M12™ Cordless LITHIUM-ION System with over 40 Cordless Tools

SPECIFICATIONS

Voltage	12V
Heat Elements	Core: R Chest, L Chest, Back
Heat Settings	3 Heat Settings Per Zone (High, Medium, Low)
Pockets	2 Lower Hand Pockets, 1 Chest Pocket for Cell Phones/Walkie Talkies, 2 Pen Pockets on Left Sleeve
Jacket Material	100% Polyester
Battery	RED LITHIUM™
No of Batteries Included	1

RELATED ARTICLES

Milwaukee® Keeps Users Safe & Warm with High Visibility M12™ Heated Jacket

REVIEW SNAPSHOT® by PowerReviews

Not yet rated. Be the first to [Write a Review](#)

RELATED ITEMS



M12™ Cordless Red Heated Jacket - Jacket Only



M12™ Cordless Red Heated Jacket Kit



M12™ Cordless Realtree AP™ Heated Jacket - Jacket Only

MORE RELATED ITEMS