



Representative

**Catalog Number:** 6N  
**Product ID:** 7TAA267320R0005  
**UPC Number:** 78378685530  
**Status:** Active

Copper Type N - Service Entrance Connector for Wire Range ACSR 8 to 8, Copper 10 Solid to 6 Stranded

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Mechanical Service Entrance Connector
Special Features	Long-lasting Connectors with bodies and Slotted Hex-Head screws made of high-strength copper alloy.
Application	Service Entrance Connector
Connection	Screw / Mechanical
Number Of Conductors	2
Material	Copper Alloy
Finish	Bare
Enclosure	None
Voltage Rating	35kV
Insulation	None
Environmental Conditions	All Seasons / Conditions
Conductor Range (Main/Primary)	ACSR #8 - #8, Copper #10 Solid - #6 Stranded
Number Of Mounting Holes	None
Mounting Hole Spacing	None
Bolt Size	1/4 inch 28 Threads

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	4x3x2.875
Outer Quantity	1000
Outer Dimensions (inches)	15x6.75x5
Weight Uom	2.38 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)