



Nothing but **HEAVY DUTY.**



# M18 ROCKET™ LED Tower Light/Charger (Tool Only)

2135-20

New



## WHAT'S INCLUDED

(1) M18 ROCKET™ LED Tower Light/Charger (Tool Only) (2135-20)

## PRODUCT DETAILS

### FEATURES

- ✓ 5 Second Setup, 7 Foot Extension.
- ✓ 3,000 Lumens of Multidirectional Light
- ✓ Impact Resistant, Reinforced Legs
- ✓ Built in M18™ Charger
- ✓ Covered AC Plug-in
- ✓ 3 Independently Pivoting Light Heads
- ✓ Protective Guard to Secure head and lens during transport and storage
- ✓ Compact footprint, Low Center of gravity
- ✓ Low Battery indicator

### SPECIFICATIONS

High Mode	3,000 Lumens   2+ hrs
Low Mode	900 Lumens   8 hrs
Voltage	18V
Length	9"
Weight	18 lbs
Height	41.5"
Width	9.5"
Tool Warranty	5 Years

### OVERVIEW

**STAND UP. LIGHT UP. CHARGE UP.** The M18™ ROCKET™ LED Tower Light/Charger is designed to deliver a lighting solution that ADAPTS, PERFORMS, and SURVIVES professional use unlike any other portable work light. The 2135-20 can be setup in seconds to a max height of 7', and collapses to less than 4' for easy transport and storage. The light head can be extended from 4-7' to light overhead work or minimize shadows when casting light downward. The multidirectional light head gives users the ability to orient the three independently pivoting

light heads to cast light in several directions. With an integrated AC plug, a user can plug in the light with a standard extension cord, and charge any M18 REDLITHIUM™ pack. Delivering 3,000 lumens, it fills up large areas with TRUEVIEW™ High Definition light. For optimized control over the output and run-time, the M18™ ROCKET™ LED Light has three settings: high provides 3,000 lumens at 2+ hours, medium provides 1,700 lumens at 4+ hours, and low provides 900 lumens at 8 hours with a M18 REDLITHIUM™ XC5.0 Battery Pack (not included).