



**M18™ Search Light (Tool Only)**












OVERVIEW



**PRODUCT DETAILS**

Spot Further, Flood Brighter. The M18™ Search Light gives users versatility, performance, and durability all in one light. Its pivoting head provides 1,250 lumens and over 700 yards of beam distance to spot objects and areas at a far distance. The search light has 4 output modes: spot mode, flood mode, spotflood mode, and strobe mode, which allow the user to spot from a far or flood an area up close. The M18 Search Light can run for up to 4 hours on flood mode and spotflood mode with an M18 REDLITHIUM™ XC 5.0 Battery Pack, and 6 hours on spot mode and 5 hours on strobe mode. Its IP54 rating provides water and dust resistance for all weather use. Its high quality LEDs never need to be replaced, and is back by a limited lifetime warranty.

**FEATURES**

-  **The Milwaukee® REDLITHIUM™ Battery Pack** is the most durable pack on the market delivering more run-time, power and longer battery life.
-  1,250 Lumens with 700 yard beam distance
-  198 Degree head rotation
-  4 output modes: Spot, Flood, SpotFlood, & Strobe
-  Spot mode: 6hrs with M18™ XC 5.0 pack
-  Flood mode: 4hrs with M18™ XC 5.0 pack
-  SpotFlood Combination mode: 4hrs with M18™ XC 5.0 pack
-  Strobe mode: 5hrs with M18™ XC 5.0 pack
-  High Definition output with true color, even beam and natural light
-  Low Battery indicator alerts users when the battery is nearing end of charge
-  IP54 Rated for All Weather Use

**SPECIFICATIONS**

Spot Mode	600 Lumens   6 hrs
Voltage	18V
Flood Mode	1,200 Lumens   4 hrs
SpotFlood Mode	1,250 Lumens   4 hrs
Strobe Mode	1,200 Lumens   5 hrs
Length	12.9"
Weight	3.1 lbs
Height	4.7"
Width	5.5"
Tool Warranty	5 Years