



Nothing but **HEAVY DUTY.**



M12™ Cordless LITHIUM-ION Grease Gun (Bare Tool)



PRODUCT DETAILS

Get up to 25% more pressure, best-in-class runtime, and compatibility with tools for drilling, fastening, lighting and cutting. The M12™ Cordless Lithium-Ion Grease Gun delivers the highest max operating pressure in its class to help you handle heavy-duty applications and eliminate downtime. It's capable of delivering more than 8,000 PSI max operating pressure for heavy machinery, cold weather applications and clogged grease fittings.

The M12 REDLITHIUM™ Battery (sold separately) lets you dispense up to seven grease cartridges per charge and is compatible with a variety of Milwaukee tools for greater workplace versatility. A lightweight, ergonomic handle offers greater comfort during prolonged use, and an onboard hose storage and shoulder strap loop offer convenience with less mess. The gun comes with a 36" flex hose with spring guard and grease coupler.

FEATURES

- ✓ Powerful 12-volt motor: Delivers more than 8,000 PSI max operating pressure
- ✓ REDLITHIUM™ Battery Technology: Superior pack construction, electronics, and performance deliver more work per charge and more work over pack life than any battery on the market
- ✓ Best-in-class runtime: Dispenses up to 7 cartridges per charge
- ✓ Integrated hose storage: Adds convenience
- ✓ Onboard fuel gauge: Helps you increase productivity and avoid interruptions
- ✓ Air bleeder valve: Priming mechanism provides quick flow
- ✓ M12™ Lithium-Ion system: Compatible with more than 20 tools for greater versatility
- ✓ Maximum durability: Backed by a 5-year warranty

SPECIFICATIONS

Voltage	12V
Length	14"
Weight	7.2 lbs
Charge Time	30 Minutes
PSI	8000 PSI
Run Time	Up to 7 Grease Cartridges per Charge
Hose Length	36"
Tool Warranty	5 Years