



Nothing but **HEAVY DUTY.**

M12™ Cordless Rotary Tool (Bare Tool)



2460-20



PRODUCT DETAILS

This compact, portable and powerful cutoff solution for the professional offers up to 10X longer life and 10% more speed. Get the power of a corded rotary tool in the M12™ Cordless Rotary Tool, which integrates high-performance motor design, optimized electronics and REDLITHIUM™ battery technology for exceptional power and durability. This compact, versatile tool offers a variable-speed of 5,000-32,000 RPM and a collet that's compatible with all 1/32" - 1/8" shank accessories for thousands of cutting, grinding, sanding and polishing solutions. Maintenance contractors, electricians, plumbers and automotive mechanics will find it indispensable for close-quarter cutoff and grinding applications.

A variable-speed dial offers fluid control, and the 1.3-pound weight permits hours of comfortable use. Grinder-style exhaust ports and front-bearing protection help this tool exceed performance and endurance expectations. The rotary tool comes with five cutting wheels, a mandrel and wrench. M12 battery sold separately.

FEATURES

- ✓ Powerful 12-volt motor: Delivers 5,000-32,000 RPM for superior speed and performance under load
- ✓ Unique Milwaukee design: Delivers up to 10X the tool life with grinder-style exhaust ports and front bearing protection
- ✓ Variable-speed dial: Offers fluid control
- ✓ 1/8" Collet: Accommodates all 1/32" - 1/8" shank accessories for thousands of applications
- ✓ Compact, lightweight design: Allows you to work comfortably in tight spaces and all day

SPECIFICATIONS

Voltage	12V
Length	9"
Weight	0.9 lbs
No Load RPM	5,000-32,000
Charge Time	30 Minutes
Tool Warranty	5 Years