



Nothing but **HEAVY DUTY.**



M18 FUEL™ 1-9/16" SDS Max Hammer Drill (Tool Only)

2717-20



WHAT'S INCLUDED

(1) M18 FUEL™ 1-9/16" SDS Max Hammer Drill (Tool Only) (2717-20)

PRODUCT DETAILS

The M18 FUEL™ 1-9/16" SDS Max Rotary Hammer is the first to world 18V SDS Max cordless solution. By utilizing proprietary M18™ and FUEL™ technologies, the 1-9/16" SDS Max rotary hammer is able to drill as fast as a corded SDS Max rotary hammers, deliver corded durability, and provide over 20 minutes of continuous chipping.

POWERSTATE™ Brushless Motor delivers 5 ft-lbs of impact energy for the more demanding, heavy-duty applications. Including dry coring and medium duty chipping in both concrete block and reinforced concrete. Powered by the new M18 REDLITHIUM HIGH DEMAND 9.0 battery pack which delivers up to 5X more run-time, 35% more power and runs 60% cooler than standard lithium-ion batteries, the 1-9/16" SDS Max rotary hammer delivers over 20 minutes of continuous chipping. It also includes REDLINK PLUS™ Intelligence, the most advanced electronic system on the market, to prevent damage to the tool and battery from overloading and overheating.

The M18 FUEL 1-9/16 SDS Max Rotary Hammer is part of Milwaukee®'s complete cordless rotary hammer solution, ranging from Compact SDS Plus to SDS Max, all powered by the M18 REDLITHIUM battery system.

FEATURES



Milwaukee® POWERSTATE™ Brushless Motor

provides more power, more run-time, and longer life.



The Milwaukee® REDLITHIUM™ Battery Pack

is the most durable pack on the market delivering more run-time, power and longer battery life.



REDLINK PLUS™ Electronic Intelligence enables advanced communication between your batteries and tools, allowing for unmatched levels of performance, protection, and productivity.

SPECIFICATIONS

Voltage	18V
Length	18.75"
Weight	12.15 lbs
No Load RPM	0-450
Height	10.1"
Width	3.0"
Blow Energy	5.1 ft-lbs
BPM	0 - 3,000
Solid Bit Capacity	1-9/16"
Handle Style	D-Handle
Tool Warranty	5 Years