



M18™ FORCE LOGIC™ 750 MCM Crimper

2778-22



WHAT'S INCLUDED

- (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack (48-11-1820)
- (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack (48-11-1850)
- (1) M18™ & M12™ Multi-Voltage Charger (48-59-1812)
- (1) Carrying Case

PRODUCT DETAILS

The M18™ FORCE LOGIC™ 750 MCM Crimper is the Easiest Way to Crimp, producing cULus classified crimps according to the UL 486A-B classification standards for #8 - 750 MCM Cu and Dual Rated Anderson, Blackburn® Burndy, Ilco, Panduit, Penn-Union and Thomas & Betts Connectors. Milwaukee® EXACT™ 12T U-Style Dies are individually engineered both for quality crimps and for faster connections on all sizes with die lengths specific to each connector. In addition, every EXACT™ 12T U-Style Die features vivid industry standard colors to indicate wire size and center alignment markings for easiest die selection and die alignment. All dies also eliminate cross referencing by imprinting the wire size onto completed connectors and are the only dies that are 100% serialized and measured for greatest accuracy and easiest inspection.

Engineered to reduce weight and improve balance, the M18 FORCE LOGIC™ 750 MCM Crimper is the lightest and only fully balanced 12T crimper, with a 350° rotating head and red alignment marks making it the Lightest, Most Balanced and Easiest Crimper to Align.

Predictive Force Monitoring (PFM™) constantly measures force output to deliver consistent speed that won't bog down on larger connectors while delivering accurate pressure, every time. The only tool that provides instant pressure verification with a green indicator. The only tool that has pre-crimp battery check that automatically ensures enough battery charge to complete each crimp. The only tool that once a crimp is engaged, has auto-complete to ensure full pressure is reached.

Milwaukee® Crimpers feature a fully enclosed high speed hydraulic pump, POWERSTATE™ Brushless Motor, REDLINK™ Electronics and REDLITHIUM™ batteries delivering Ultimate Reliability in tough conditions.

Featuring Milwaukee® ONE-KEY™ Technology, Milwaukee® Crimpers enable you to store real time crimp data, generate professional reports, view historical tool performance data and sync it all wirelessly to the cloud for easy access. Like all ONE KEY™ tools Milwaukee® Crimpers feature tool tracking, allowing you to pinpoint missing tools quicker and inventory management, which creates a central place for you to track all tools and equipment across your network of jobs and users.

FEATURES



Milwaukee® POWERSTATE™ Brushless Motor
provides more power, more run-time, and longer life.



The Milwaukee® REDLITHIUM™ Battery Pack
is the most durable pack on the market delivering more run-time, power and longer battery life.



REDLINK PLUS™ Electronic Intelligence
enables advanced communication between your batteries and tools, allowing for unmatched levels of performance, protection, and productivity.

- ✔ Lightest 12T Crimper
- ✔ Most Balanced with Ergonomic Grip Design
- ✔ Bold Alignment Marks aid accuracy in crimp placement
- ✔ PFM™ (Predictive Force Monitoring) with Auto Complete Ensures Full Pressure
- ✔ PFM™ (Predictive Force Monitoring) Provides Instant Pressure Verification with Green Indicator
- ✔ Pre-Crimp Battery Check Automatically Ensures Enough Charge to Complete Each Crimp
- ✔ 350° Head Rotation Provides Easy Access in Tight Spaces
- ✔ The Tool Records & Stores Every Crimp Made for Professional Report Building through ONE KEY™
- ✔ Longer Life with POWERSTATE™ Brushless Motor & Weather Protected Electronics that Keep Dirt, Dust & Moisture Out

SPECIFICATIONS

Voltage	18V
Battery	M18™ REDLITHIUM™
Battery Warranty	3 Year
ONE-KEY Enabled	Yes
Length	16.0"
Capacity	750MCM Cu / Al
Head Rotation	350 degrees
Adaptive Pressure Control System	Yes
Reporting and Tool Diagnostics	Yes
Full Pressure Indicator	Yes
Tool Warranty	5 Years