



Nothing but **HEAVY DUTY.**



## M18 FUEL™ 1/2" Mid-Torque Impact Wrench with Pin Detent (Tool Only)

2860-20



### WHAT'S INCLUDED

- (1) Belt Clip
- (1) M18 FUEL™ 1/2" Mid-Torque Impact Wrench with Pin Detent (Tool Only) (2860-20)

### PRODUCT DETAILS

Delivering 450 ft-lbs Fastening torque and 600 ft-lbs Nut-Busting torque, the M18 FUEL™ Mid-Torque Impact Wrench is more powerful while also being up to 4" shorter and up to 2 lbs lighter than many competitive impact wrenches. The POWERSTATE™ Brushless Motor delivers up to 0- 2,400 RPM resulting in increased productivity. REDLINK PLUS™ Intelligence is the most advanced electronic system on the market, preventing damage to the tool and battery caused by overloading or overheating. For use with REDLITHIUM™ Compact Batteries or Extended Capacity Batteries (sold separately), the M18 FUEL™ Mid-Torque delivers more work per charge and more work over the life of the pack than competitive batteries on the market. The 3-Mode DRIVE CONTROL™ provides greater control over output speed and power for greater versatility. At 6.7" in length and 5.3lbs w/ a 5.0Ah battery, the M18 FUEL 1/2" Mid-Torque Impact Wrench delivers the balance and weight desired by professionals for all day use. This tool includes a 1/2" Pin Detent anvil which provides superior socket retention. A new overmold material gives you ultimate comfort during prolonged use while lasting longer against corrosive materials.

### FEATURES



**Milwaukee® POWERSTATE™ Brushless Motor**  
provides more power, more run-time, and longer life.



**The Milwaukee® REDLITHIUM™ Battery Pack**  
is the most durable pack on the market delivering more run-time, power and longer battery life.



**REDLINK PLUS™ Electronic Intelligence**  
enables advanced communication between your batteries and tools, allowing for unmatched levels of performance, protection, and productivity.



Delivers up to 450 ft-lbs of Fastening Torque



Delivers up to 600 ft-lbs of Nut-Busting Torque



3-Mode DRIVE CONTROL™ provides greater control over output speed and power with a max RPM of 2,400



Compact length at 6.7" to allow for more access in tight spaces



Lightweight tool at 5.3lbs w/ 5.0Ah battery for less fatigue  
improved rubber overmold to withstand corrosive materials



LED Light Included



Utilizes a Pin Detent design for maximum socket retention

### SPECIFICATIONS

Voltage	18V
Length	6.77"
Weight	3.8 lbs
LED Light	Yes
Height	8.2"
Width	2.7"
Tool Warranty	5 Years