



PRODUCT DETAILS

Milwaukee® S&D Black Oxide drill bits are designed for extreme durability and long life. A specially designed parabolic flute form clears chips fast, while the 3-Flat Secure-Grip™ shank holds the bit firmly in the drill chuck. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Effective for drilling on curved surfaces, Milwaukee® Black Oxide bits require less effort to drill through metal, wood and PVC, and are highly recommended for use with portable drills.

FEATURES

- ✓ Fast, accurate drilling: 135° split point tip starts on contact to prevent walking, while the parabolic flute clears chips fast
- ✓ Reduced slipping: 3-Flat Secure-Grip™ shank holds the bit firmly in the drill chuck
- ✓ Corrosion resistant: Black oxide coating provides lubricity and resists corrosion of the bit
- ✓ Versatile: Reduced shank diameter for use in 1/2" chucks

SPECIFICATIONS

Pack Qty	1 Pack
Shank	3-Flat (1/2")
Diameter	3/4"
Coating	Black Oxide
Length	6"
Flute Length	3"
Size	3/4"
Decimal Equivalent	0.75
Application	Metal Wood Plastic