

# MINKA-LAVERY®

Job Name:
Job Type:
Quantity:

Family:	Aspen™ II
Product Category:	BATH
Item#:	5972-1-138
Finish:	Aspen Bronze™
Certification:	E87611-YCL



## Lamping

Number of Bulbs:	2
Light Type:	A19
Socket Type:	Medium
Max Bulb Wattage:	100
Bulbs Included:	0
Color Temp:	N/A
Photo Cell Included:	N/A
Ballast:	N/A
Dimmable:	N

## Shipping

Carton Weight:	9.7
Carton Width:	9.5
Carton Height:	14
Carton Length:	16.5
Carton Cubic Feet:	1.27
Master Pack:	1
Master Pack Weight:	N/A
Master Pack Width:	N/A
Master Pack Height:	N/A
Master Pack Length:	N/A
Master Cubic Feet:	N/A
*Multi-Pack:	1
Small Package Shippable:	Y

\*For additional information, please contact Customer Care: 1-800-221-7977.

## Measurements

Width:	16
Height:	9.75
Length:	N/A
Min Overall Height:	N/A
Max Overall Height:	N/A
Height Adjustable:	N
Extension:	9
Net Weight:	8.47
Back Plate/Canopy Width:	6.75
Back Plate/Canopy Height:	4.38
Canopy Length:	N/A
Center to Top of Fixture:	7
Center to Bottom of Fixture:	2.75
Slope:	N
Chain Length:	N/A
Wire Length:	7

## Shade

*Shade Description:	Rustic Scavo Glass
*Shade Material:	GLASS
*Shade Quantity:	2
*Shade Number:	G5971
*Shade Width:	6.13
*Shade Height:	4.5
*Shade Length:	N/A

## Miscellaneous

Safety Cable Included:	N
------------------------	---

## Notes

--

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.