

MINKA-LAVERY®

Job Name:
Job Type:
Quantity:

Family:	City Square
Product Category:	BATH
Item#:	6543-77
Finish:	CHROME
Certification:	3057374



Lamping

Number of Bulbs:	3
Light Type:	A-19,MED
Socket Type:	E26,MED
Max Bulb Wattage:	100
Bulbs Included:	0
Color Temp:	N/A
Photo Cell Included:	N/A
Ballast:	N/A
Dimmable:	N

Shipping

Carton Weight:	6.38
Carton Width:	6.5
Carton Height:	9.5
Carton Length:	22
Carton Cubic Feet:	0.786
Master Pack:	1
Master Pack Weight:	N/A
Master Pack Width:	N/A
Master Pack Height:	N/A
Master Pack Length:	N/A
Master Cubic Feet:	N/A
*Multi-Pack:	N/A
Small Package Shippable:	Y

*For additional information, please contact Customer Care: 1-800-221-7977.

Measurements

Width:	20.75
Height:	7
Length:	N/A
Min Overall Height:	N/A
Max Overall Height:	N/A
Height Adjustable:	N
Extension:	5
Net Weight:	4.63
Back Plate/Canopy Width:	6
Back Plate/Canopy Height:	4.5
Canopy Length:	N/A
Center to Top of Fixture:	6
Center to Bottom of Fixture:	2.13
Slope:	N
Chain Length:	N/A
Wire Length:	7"

Shade

*Shade Description:	Etched Opal Glass
*Shade Material:	GLASS
*Shade Quantity:	3
*Shade Number:	G6541
*Shade Width:	3.75
*Shade Height:	5.38
*Shade Length:	N/A

Miscellaneous

Safety Cable Included:	N
------------------------	---

Notes

--

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.