

# the great outdoors<sup>®</sup>

by MINKA-LAVERY<sup>®</sup>

Job Name:
Job Type:
Quantity:

Family:	Berkeley™
Product Category:	OUTDOOR PIER MOUNT
Item#:	8567-51-PL
Finish:	RUST (CHEMICAL)
Certification:	3057374



### Lamping

Number of Bulbs:	1
Light Type:	SEMISPIRAL26W,SELF-BALLASTGU24
Socket Type:	GU24
Max Bulb Wattage:	26
Bulbs Included:	1
Color Temp:	2700
Photo Cell Included:	N/A
Ballast:	INTEGRAL
Dimmable:	N

### Shipping

Carton Weight:	15.44
Carton Width:	14.5
Carton Height:	21.75
Carton Length:	14.5
Carton Cubic Feet:	2.64
Master Pack:	1
Master Pack Weight:	N/A
Master Pack Width:	N/A
Master Pack Height:	N/A
Master Pack Length:	N/A
Master Cubic Feet:	N/A
*Multi-Pack:	1
Small Package Shippable:	Y

\*For additional information, please contact Customer Care: 1-800-221-7977.

### Notes

--

### Measurements

Width:	11.5
Height:	18.75
Length:	11.5
Min Overall Height:	0
Max Overall Height:	0
Height Adjustable:	N
Extension:	N/A
Net Weight:	11.90
Back Plate/Canopy Width:	0
Back Plate/Canopy Height:	0
Canopy Length:	N/A
Center to Top of Fixture:	0
Center to Bottom of Fixture:	0
Slope:	N
Chain Length:	N/A
Wire Length:	7

### Shade

*Shade Description:	Double French Scavo
*Shade Material:	Glass
*Shade Quantity:	4
*Shade Number:	G8563-1
*Shade Width:	N/A
*Shade Height:	N/A
*Shade Length:	N/A

### Miscellaneous

Safety Cable Included:	N
------------------------	---

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.