

MINKA-LAVERY®

Job Name:
Job Type:
Quantity:

Family:	Paradox™
Product Category:	FLUSH MOUNT
Item#:	893-84-PL
Finish:	BRUSHED NICKEL
Certification:	E301845 004292



Lamping

Number of Bulbs:	3
Light Type:	13W/ SPIRAL CFL
Socket Type:	GU24 Twist Lock
Max Bulb Wattage:	13
Bulbs Included:	3
Color Temp:	N/A
Photo Cell Included:	N/A
Ballast:	N/A
Dimmable:	N

Shipping

Carton Weight:	5.5
Carton Width:	15.75
Carton Height:	6.75
Carton Length:	15.75
Carton Cubic Feet:	0.969
Master Pack:	1
Master Pack Weight:	N/A
Master Pack Width:	N/A
Master Pack Height:	N/A
Master Pack Length:	N/A
Master Cubic Feet:	N/A
*Multi-Pack:	1
Small Package Shippable:	Y

*For additional information, please contact Customer Care: 1-800-221-7977.

Measurements

Width:	15
Height:	6
Length:	N/A
Min Overall Height:	N/A
Max Overall Height:	N/A
Height Adjustable:	N
Extension:	N/A
Net Weight:	4.41
Back Plate/Canopy Width:	N/A
Back Plate/Canopy Height:	N/A
Canopy Length:	N/A
Center to Top of Fixture:	N/A
Center to Bottom of Fixture:	N/A
Slope:	N
Chain Length:	N/A
Wire Length:	7

Shade

*Shade Description:	Etched Marble Glass
*Shade Material:	GLASS
*Shade Quantity:	1
*Shade Number:	G893
*Shade Width:	11.88
*Shade Height:	3.5
*Shade Length:	N/A

Miscellaneous

Safety Cable Included:	N
------------------------	---

Notes

--

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.