

Job Name:
Job Type:
Quantity:

Family:	Suspended
Product Category:	Pendants
Item#:	P593-084
Finish:	Brushed Nickel
Certification:	E87611CCC



Lamping

Number of Bulbs:	6
Light Type:	A19 Med
Socket Type:	E27 Med
Max Bulb Wattage:	100
Bulbs Included:	0
Color Temp:	N/A
Photo Cell Included:	N/A
Ballast:	N/A
Dimmable:	Y

Shipping

Carton Weight:	38.06
Carton Width:	36.5
Carton Height:	14
Carton Length:	36.5
Carton Cubic Feet:	10.794
Master Pack:	1
Master Pack Weight:	N/A
Master Pack Width:	N/A
Master Pack Height:	N/A
Master Pack Length:	N/A
Master Cubic Feet:	N/A
*Multi-Pack:	1
Small Package Shippable:	N

*For additional information, please contact Customer Care: 1-800-221-7977.

Notes

Measurements

Width:	34.5
Height:	26.5
Length:	N/A
Min Overall Height:	34.5
Max Overall Height:	70.5
Height Adjustable:	Y
Extension:	N/A
Net Weight:	26.63
Back Plate/Canopy Width:	N/A
Back Plate/Canopy Height:	1
Canopy Length:	N/A
Center to Top of Fixture:	N/A
Center to Bottom of Fixture:	N/A
Slope:	Y
Chain Length:	N/A
Wire Length:	7

Shade

*Shade Description:	White Frosted
*Shade Material:	Glass
*Shade Quantity:	N/A
*Shade Number:	MULTIPLE SHADES
*Shade Width:	N/A
*Shade Height:	N/A
*Shade Length:	N/A

Miscellaneous

Safety Cable Included:	N
------------------------	---