


















Residential & Commercial Princess

	SPRAYED BRASS MATTE	CHROME PLATED	IVORY SEMI- GLOSS	WHITE WRINKLE	WHITE SEMI- GLOSS	BROWN WRINKLE	IVORY WRINKLE
 One 1/4" ID Phone (Box Mntg. 3.281") (01)*	71201	73201	74201	75201	76201	78201	79201
 Two 1/4" ID Phones (Box Mntg. 3.281") (02)*	71202	73202	74202	75202	76202	78202	79202
 One 1/4" ID Phone with Metal Bushing (Box Mntg. 3.281") (61)*	71591	73591	74591	75591	76591	78591	79591
 One Phone with .375" ID Grommet and Mounting Strap (Device Mntg. 2.375")*	71181	73181	74181	75181	76181	78181	79181
 One Phone 1.405" with 1" ID Plastic Bushing (Box Mntg. 3.281") (71)*	71581	73581	74581	75581	76581	78581	79581
 One 20A TL Recept. 1.620" ID Hole (3R)	71111	73111	74111	75111	76111	78111	79111
 Two 20A TL Recepts. 1.620" ID Hole Must Use 3 Gang Plate (23R)	71113	73113	74113	75113	76113	78113	79113
 One 30A 3 & 4 Wire TL Recept. 1.730" ID Hole (333OR)	71229	73229	74229	75229	76229	78229	79229
 30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole (3D)	71221	73221	74221	75221	76221	78221	79221
 30/50A 3 Wire, Range/Dryer Recept. 2.125" ID Hole 2 Gang Plate (23D)	71222	73222	74222	75222	76222	78222	79222
 30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole (N23D)	71227	73227	74227	75227	76227	78227	79227
 30/50/60A 3 & 4 Wire Recepts. 2.480" ID Hole (5R)	71223	73223	74223	75223	76223	78223	79223
 30/50/60A 4 Wire for Leviton 278 & 279 Recepts. 2.625" ID Hole (L5R)	71225	73225	74225	75225	76225	78225	79225
 30/50/60A 4 Wire Offset Recepts., 2.275" ID Hole (N5RR)	71226	73226	74226	75226	76226	78226	79226
 30/50/60A 4 Wire Recepts. 2.255" ID Hole (P5R)	71228	73228	74228	75228	76228	78228	79228
 Louver, Horizontal (Device Mntg. 2.375") (LH)	71630	73630	74630	75630	76630	78630	79630
 Louver, Vertical (Device Mntg. 2.375") (LV)	71631	73631	74631	75631	76631	78631	79631
 2 Louvers (Device Mntg. 2.375") (2LV)	71632	73632	74632	75632	76632	78632	79632