



Dependable Power for Any Application

Product Datasheet

316 Stainless Steel - 240 X 480 Primary Volts - 120/240
Secondary Volts - Four Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

Catalog #: T253013SS



PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	3.00
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	2
Taps % Steps:	2.5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	11.50 (29.2)
Width (In./cm):	10.31 (26.2)
Depth (In./cm):	7.13 (18.1)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Weather Shield:	WSA1
Wiring Diagram:	3

PACKAGING

Ship Weight (Lbs/Kg):	55 (24.9)
-----------------------	-----------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf