



Actual

Catalog Number: 13-263
Product ID: 7TCA008010R0061
UPC Number: 78378613263
EAN Number: 05414363201335
Status: Active

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 289.56mm (11.4 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), 50 Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	T&B Electricians' Supplies
Type	Cable Tie
Application	For Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications
Standard	UL E49405
Width	0.14 Inches/3.556mm
Length	11.4 Inches/289.56mm
Thickness	0.046 Inches/1.17mm
Bundle Diameter	Max 3 Inches/76.2 mm
Material	Polyamide/Nylon 6.6
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	180 Newtons (40 Pounds)

Packaging

Inner Quantity	50
Outer Quantity	500
Outer Dimensions (inches)	16.3x6.9x4.5
Weight Uom	5 lbs. per 1000

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com