



Actual

Catalog Number: 2B10X
Product ID: 7TAH006160R0006
UPC Number: 78378640008
Status: Active

Copper Type 2BX - One piece Two-Bolt Connector without spacer for Wire Range Main: 2 - 1/0 Str. Tap: 10 Sol. - 1/0 Str. , Bolt Size 1/2

- Single-piece construction. Castings and bolts of high-strength copper alloy. Neoprene washer holds free bolt in place during installation.
- UL 486A listed for copper conductor only.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Two-Bolt Connector
Special Features	Single-piece construction. Castings and bolts of high-strength copper alloy. Neoprene washer holds free bolt in place during installation.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	2 - 1/0 Str
Conductor Range (Tap/Secondary)	10 Sol - 1/0 Str
Bolt Size	42737

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Quantity	25
Inner Dimensions (inches)	5x3.37x6.5
Outer Quantity	250
Outer Dimensions (inches)	10.56x7.25x19.12
Weight Uom	20 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com