



Actual

Catalog Number: ADR25-32
Product ID: 7TAH006600R0209
UPC Number: 78378661013
Status: Active

Type ADR-ALCUL Three-Conductor, Two-Hole Mount for Conductor Range Max 250 kcmil, Min 6 Str.

- Easy Installation - no special tools required.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Dual-Rated Mechanical Connector
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Number Of Conductors	3
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	6-250
Number Of Mounting Holes	2

Packaging

Inner Quantity	6
Inner Dimensions (inches)	4.5x4.5x3.2
Outer Quantity	60
Weight Uom	55.31 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com