



Actual

**Catalog Number:** CF44-1  
**Product ID:** 7TAA267230R0008  
**UPC Number:** 78378607619  
**EAN Number:** 05414363149330  
**Status:** Active

Copper H-Type Compression Connector Main: 6 TR. 4, 6 Solid Copper, Tap: 8, 4, 6 Solid Copper, Tap: 6 Stranded Copper

### North American Specifications (UNSPSC)

UNSPSC	39121448 Wire or cable compression connector
IGCC	4668 Wire or cable compression connector
Brand Name	Blackburn
Type	H-Type Compression Connector
Special Features	Efficient Design Requires Less Crimping Force. Full Length Tab makes Installation Easy. Installs with Standard Compression Tools and Dies. RUS Accepted.
Conductor Range	Tap .128-.204 inch
Material	Electrolytic Copper
Conductor Type	Crimp
Conductor Range (Main/Primary)	.162-.204 inch
Bolt Size	N/A
Mounting Hole Spacing	N/A

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	4.75x5.25x3
Outer Quantity	600
Outer Dimensions (inches)	11.5x11x5.7
Weight Uom	5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000520

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)