



Actual

Catalog Number: HMC5750-LI
Product ID: 7TAA131540R0012
UPC Number: 78378653046
EAN Number: 05415022359497
Status: Active

6-Ton Lithium-Ion Battery Powered Dieless Closed Crimp Tool for Crimping #6-750 kcmil Cu/Al Connectors

- 14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge
- Visual indication of complete crimp compression (green/orange/red)
- All tools and batteries come with a standard 5-year warranty
- Covers a wide range of applications in both the electrical and utility markets
- Dieless tool with a 180 degree rotating head, uses one stationary and three movable indenting nibs, which close at 90 degree angles to each other so that the connector is squeezed equally at four strategic points

North American Specifications (UNSPSC)

UNSPSC	27112750 Battery powered crimping tool
IGCC	2388 Battery powered crimping tool
Brand Name	Blackburn
Type	Battery Power Crimp Tool
Special Features	14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge

Packaging

Outer Quantity	1
Outer Dimensions (inches)	6.25x4.5x12.87
Weight Uom	26.66 lbs. Each

Documents / Support Tools

Technical Data Sheet Global	wsd-001156
Instruction Sheet 1	ta04748-tb2
Instruction Sheet 2	ta04683-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com