



Actual

Catalog Number: SP2SS
Product ID: 7TAA014450R0015
UPC Number: 78378612150
Status: Active

Short Stud Single Service Post Connectors for Conductors 5 - 10 Stranded, 4 - 10 Solid, Stud Size 5/16 - 18 x 5/8

- Hex design bolts are machined from high-conductivity bronze alloy.
- Nuts and pressure bars are cold-formed from high-strength copper or copper alloy.
- For copper to copper connections, for grounding of steel structures or transformers using one or two cables, for tapping one or two cables from bus bar.

North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Mechanical Grounding
Special Features	Hex design bolts are machined from high-conductivity bronze alloy.
Application	For copper to copper connections, for grounding of steel structures or transformers using one or two cables, for tapping one or two cables from bus bar.
Standard	UL E9809, CSA 6591
Conductor Size	5 - 10 Str, 4 - 10 Sol
Conductor Material	Copper

Packaging

Inner Quantity	100
Inner Dimensions (inches)	4.75x5.25x3.5
Outer Quantity	1000
Outer Dimensions (inches)	18.87x11.38x5.63
Weight Uom	5.63 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com