

# Bare Copper

Soft Drawn Bare Copper Wire



Meets or exceeds  
**ASTM-B3, ASTM-  
B8, or ASTM-B787**

## APPLICATIONS

For use in overhead transmission and distribution applications. Also for use in grounding applications.

## CONDUCTORS

Solid conductors uncoated copper per ASTM-B3

Stranded conductors 8 AWG – 2 AWG and 250 MCM – 750 MCM uncoated copper per ASTM-B3 and ASTM-B8

Stranded conductors 1 AWG – 4/0 AWG – uncoated copper conductors per ASTM B3 and ASTM-B787

## INDUSTRY STANDARDS\*

ASTM B3

ASTM B8

ASTM-B787

RoHS Compliant



MADE IN THE USA

©2012, Cerro Wire LLC  
All Rights Reserved

\*It is the sole responsibility of the end user to determine suitability of this product for its intended end use and application.

**cerrowire**<sup>®</sup>

Electrical Distribution Division: 800.523.3869 | FAX 877.877.9563  
Consumer Markets Division: 866.572.3776 | FAX 812.793.2626  
www.cerrowire.com

A Marmon Group/  
Berkshire Hathaway Company

## Bare Copper

### Soft Drawn Bare Copper Wire

Product Code Number	AWG Size	No. of Strands	Diam. Each Inches	Approx. Overall Diam. Inches	Approx. Net Wt. Lbs./M Ft.
050-2000x	8	Solid	.1285	.1285	50
050-2215x	6	Solid	.1620	.1620	79
050-2200x	6	Solid	.1620	.1620	79
050-2400x	4	Solid	.2043	.2043	126
050-2600x	2	Solid	.2576	.2576	201
050-4000x	8	7	.0486	.146	50
050-4200x	6	7	.0612	.184	80
050-4215x	6	7	.0612	.184	80
050-4400x	4	7	.0772	.232	127
050-4600x	2	7	.0974	.292	202
050-4700x	1	19	.0710, .0568	.323	255
050-5000x	1/0	19	.0807, .0591	.360	323
050-5200x	2/0	19	.0906, .0663	.404	404
050-5400x	3/0	19	.1017, .0745	.454	509
050-5600x	4/0	19	.1142, .0836	.510	643
050-6000x	250	37	.0850, .0654	.545	744
050-6400x	300	37	.0935, .0701	.597	895
050-6800x	350	37	.1000, .0799	.644	1,040
050-7200x	400	37	.1077, .0815	.686	1,170
050-8000x	500	37	.1192, .0973	.786	1,484
050-8400x	600	61	.0989	.866	1,792
050-8800x	750	61	.1114	.968	2,285

## Bare Copper

### Soft Drawn Bare Copper Wire

Package Code	D	H	I	J	K	P	S*	X*
AWG Size	125' Spool	200' Spool	315' Spool	500' Reel	1,000' Reel	5,000' Reel	SPEC Size	SPEC Cut Avail.
8 Solid				X		X		
6 Solid			X		X	X		
4 Solid		X		X	X			
2 Solid	X							
8-7 STR				X	X			
6-7 STR			X		X			
4-7 STR		X			X			
3-7 STR								
2-7 STR	X				X			
1-19 STR								X
1/0-19 STR				X	X			
2/0-19 STR				X	X			
3/0-19 STR				X	X			
4/0-19 STR				X	X			
250-37 STR								X
350-37 STR								X
500-37 STR								X
750-37 STR								X

\* No special cuts less than 50'