



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1530 Shields Drive  
 Waukegan, IL 60085  
 Toll-Free (800) 323-9355  
 Fax: (847) 689-1192

**PART NUMBER:** 96263  
**DESCRIPTION:** 24 AWG /4 Pair CMR CATEGORY 5e DATA CABLE  
**COMPLIANCE:**

- ETL Listed Type CMR
- C(ETL) listed CMG FT4
- ETL Verified to TIA/EIA 568-C.2
- Meets or exceeds TIA/EIA 568-C.2

## Construction Parameters:

		<u>DIAMETER*</u>
Conductor	24 AWG Solid Bare Copper	0.020
Dielectric	Solid PE	0.036
Assembly	Each pair has different lay length for cross-talk prevention and ripcord added.	
Jacket	PVC	0.200

\* = Nominal value

## Product Electrical Characteristics:

Freq. (MHz)	Attn. (dB/100m) Max	NEXT loss (dB) Min	PSNEXT loss (dB) Min	ACR (dB@100m) Min	PSACR (dB@100m) Min	ELFEXT (dB@100m) Min	PSELFEXT (dB@100m) Min	Ret. Loss (dB) Max	Specification	Value
1	2.0	65.3	62.5	63.3	60.3	63.8	60.8	20.0	Mutual Capacitance: (nF / 100m) Nominal	4.4
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	25.0	DC Resistance: (Ohms / 100m @ 20°C) Max	8.9
16	8.2	47.3	44.3	39.1	36.1	39.7	36.7	25.0	Delay Skew: (ns / 100m) Max	45
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	25.0	Velocity of Propagation: Non-Plenum (%)	70
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	23.6	Plenum (%)	72
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	21.5	Input Impedance: (Ohms @ 1-100 MHz)	100 +/- 15
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	20.1		

Pair Colors: W/BL with BL, W/OR with O, W/GR with GR, W/BR with BR  
 Jacket Color: Standard colors are Blue and Gray

Legend (Ink Print) CAT5E COLEMAN CABLE 96263 CAT5E 24 AWG 4PR UTP C(ETL)US LISTED 2003548 TYPE CMX-OUTDOOR OR CMR FT-4 TESTED TO 350 MHZ ETL VERIFIED TO TIA/EIA-568-C.2 CAT 5E  
*(Also printed with sequential footage & date code)*

This product complies with European Directive 2002/95/EC (RoHS)  
 On special orders, the customer will accept all mil lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control, all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name \_\_\_\_\_

Customer Approval \_\_\_\_\_

Specification Issue Date: August 17, 2010