

UF-B



MULTIPLE CONDUCTOR										
CONDUCTOR			JACKET THICKNESS (MILS)	WITH GROUND				WITHOUT GROUND		ALLOWABLE AMPACITY
SIZE (AWG)	NO. STRANDS	INSULATION AND JACKET THICKNESS (MILS)		GROUND WIRE		CABLE DIMENSION (MILS)	APPROX NET WEIGHT PER 1000' (LBS.)	CABLE DIMENSION (MILS)	APPROX. NET WEIGHT PER 1000' (LBS)	
				SIZE AWG	NO. STRANDS					
TWO CONDUCTOR										
14	1	19	30	14	1	423 x 168	70	354 x 168	57	15
12	1	19	30	12	1	463 x 183	95	386 x 183	70	20
10	1	24	30	10	1	519 x 215	138	440 x 215	102	30
8	7	35	45	10	1	678 x 302	222	576 x 302	178	40
6	7	35	45	10	1	770 x 338	303	668 x 338	256	55
THREE CONDUCTOR										
14	1	19	30	14	1	581 x 168	96	501 x 168	74	15
12	1	19	30	12	1	626 x 183	129	581 x 183	108	20
10	1	24	30	10	1	727 x 215	191	661 x 215	156	30
8	7	35	45	10	1	1059 x 319	344	984 x 319	304	40
6	7	35	45	10	1	1223 x 361	478	1153 x 361	437	55

NOTE: Contact supplier for Single Conductor.