



Part Number	Size	T Min.	OD	□val.	E	B	D Min.	L Min.
A55BA42	1"	0.060"	1.315"	0.060"	1.331"	1.320"	1.000"	240"
A55BE42	1 1/2"	0.060"	1.900"	0.060"	1.921"	1.906"	1.375"	240"
A55CA42	2"	0.077	2.375"	0.060"	2.400"	2.381"	1.750"	240"
A55DA42	3"	0.118"	3.500"	0.060"	3.538"	3.508"	2.875"	240"
A55EA42	4"	0.154"	4.500"	0.100"	0.100"	4.509"	3.375"	240"
A55FA42	5"	0.191"	5.563"	0.100"	0.100"	5.573"	4.000"	240"
A55GA42	6"	0.227"	6.625"	0.100"	0.100"	6.636"	5.000"	240"

Dimensions are Nominal. See NEMA TC 6&8 for tolerance.

Meets requirements of NEMA TC 6&8.  
 Meets ASTM F-512.  
 Material is Rigid PVC  
 Bells are clearance fit.  
 For Direct Bury only.  
 Spigot I.D. is chamfered.

**CANTEX**

INC.

Fort Worth, TEXAS

DB-120 Rigid PVC Conduit  
 High Modulus 500,000 psi