



RIGID PVC UTILITY DUCT RATED FOR 90 DEGREE CELSIUS WIRE TYPE DB-60 FOR DIRECT BURIAL

NEMA TC-6 DB-60

Trade Size	Part No.	O.D.	Min. Wall	Weight /foot	Ft/ lift
2	7508	2.375	.060	.361	2800'
3	7512	3.500	.092	.716	1760'
4	7516	4.500	.121	1.171	1140'
5	7520	5.563	.152	1.778	760'
6	7524	6.625	.182	2.500	520'

SPECIAL INFORMATION

1. 20' lengths are standard, 10' lengths available on special request.
2. Minimum shipment: full pallet quantity per size.

RIGID PVC UTILITY DUCT RATED FOR 90 DEGREE CELSIUS WIRE TYPE DB-120 FOR DIRECT BURIAL

NEMA TC-8 DB-120

Trade Size	Part No.	O.D.	Min. Wall	Weight /foot	Ft/ lift
2	6108	2.375	.077	.371	2800'
3	6112	3.500	.118	.836	1760'
4	6116	4.500	.154	1.402	1140'
5	6120	5.563	.191	2.150	760'
6	6124	6.625	.227	3.045	520'

SPECIAL INFORMATION

1. 20' lengths are standard, 10' lengths available on special request.
2. Minimum shipment: full pallet quantity per size.

