



Formerly Georgia Pipe

RIGID PVC UTILITY DUCT RATED FOR 90 DEGREE CELSIUS WIRE TYPE EB-20 FOR ENCASED BURIAL

NEMA TC-6 EB-20

Trade Size	Part No.	O.D.	Min. Wall	Weight /foot	Ft/ lift
2	2008	2.375	.060	.361	2800'
3	2012	3.500	.061	.514	1760'
4	2016	4.500	.082	.843	1140'
5	2020	5.563	.103	1.268	760'
6	2024	6.625	.125	1.729	520'

SPECIAL INFORMATION

1. 20' lengths are standard, 10' lengths available on special request.
2. Minimum shipment: full pallet quantity per size.

RIGID PVC UTILITY DUCT RATED FOR 90 DEGREE CELSIUS WIRE TYPE EB-35 FOR ENCASED BURIAL

NEMA TC-8 EB-35

Trade Size	Part No.	O.D.	Min. Wall	Weight /foot	Ft/ lift
2	3508	2.375	.060	.361	2800'
3	3512	3.500	.076	.533	1760'
4	3516	4.500	.100	.923	1140'
5	3520	5.563	.126	1.437	760'
6	3524	6.625	.152	2.064	520'

SPECIAL INFORMATION

1. 20' lengths are standard, 10' lengths available on special request.
2. Minimum shipment: full pallet quantity per size.

