


# Sch 40/Sch 80 Swedge Couplings



## Schedule 40

Size	Dimensions (inches)					
	M (Max)	B (Min)	C (Min)	D (Min)	N (Min)	E (Min)
2"	2.405	2.357	1.125	2.079	$\frac{3}{32}$	0.130
2 ½"	2.905	2.853	1.469	2.484	$\frac{3}{16}$	0.165
3"	3.530	3.477	1.594	3.083	$\frac{3}{16}$	0.179
4"	4.565	4.476	1.750	4.076	$\frac{3}{16}$	0.197
5"	5.643	5.523	1.937	5.097	$\frac{3}{16}$	0.214
6"	6.708	6.584	2.125	6.115	$\frac{1}{4}$	0.232

## Schedule 80

Size	Dimensions (inches)					
	M (Max)	B (Min)	C (Min)	D (Min)	N (Min)	E (Min)
2"	2.405	2.357	1.125	2.079	$\frac{3}{32}$	0.181
3"	3.530	3.477	1.594	3.083	$\frac{3}{16}$	0.249