

Jacketed Cables Unshielded, Plenum Rated

Applications: Wiring Burglar Alarm, Public Address Systems, Intercoms, Telephone Stations, Speakers, Instrumentation, Control and other Low Voltage Circuits that are Power-Limited.

Code Restrictions: OK for use with all Power-Limited Circuits.

Features: Available In 500 foot or 1000 foot Tangle-Free Boxes or Spools. Sequential Footage Markings.

Construction: Copper Conductors, Low Smoke PVC insulation, Low Smoke PVC Jacket. Standard Jacket Color: Natural. Conductor Color Code Chart 1 (up to 12 conductors). Color Code Chart 2 (13 conductors and over).



JACKETED CABLES UNSHIELDED, PLENUM RATED 60° C

AWG #/COND.	STR/SOL	NOM. O.D.	NOM. CAP. PF/FT	LISTINGS	AVG. WT. PER MFT	PART#
22	2	SOL.	.104	24	C(UL), FT6, CMP, CL2P	10 (LBS.) 3101*
22	2	STR.	.114	24	C(UL), FT6, CMP, CL2P	11 (LBS.) 3102*
22	3	STR.	.120	25	C(UL), FT6, CMP, CL2P	15 (LBS.) 3127
22	4	SOL.	.116	24	C(UL), FT6, CMP, CL2P	15 (LBS.) 3103*
22	4	STR.	.133	24	C(UL), FT6, CMP, CL2P	17 (LBS.) 3104*
22	5	STR.	.145	24	C(UL), FT6, CMP, CL2P	20 (LBS.) 3105*•
22	6	STR.	.158	24	C(UL), FT6, CMP, CL2P	24 (LBS.) 3106*
22	8	STR.	.172	24	C(UL), FT6, CMP, CL2P	30 (LBS.) 3107
22	10	STR.	.200	24	C(UL), FT6, CMP, CL2P	37 (LBS.) 3108+
22	12	STR.	.204	24	C(UL), FT6, CMP, CL2P	43 (LBS.) 3109+
22	15	STR.	.232	24	C(UL), FT6, CMP, CL2P	53 (LBS.) 3110
20	2	STR.	.132	27	C(UL), FT6, CMP, CL2P	15 (LBS.) 3112
20	3	STR.	.140	28	C(UL), FT6, CMP, CL2P	20 (LBS.) 3128
20	4	STR.	.155	27	C(UL), FT6, CMP, CL2P	25 (LBS.) 3113
18	2	STR.	.148	30	C(UL), FT6, CMP, CL2P	19 (LBS.) 3114
18	2	SOL.	.136	30	C(UL), FT6, CMP, CL2P	18 (LBS.) 3134
18	3	STR.	.159	29	C(UL), FT6, CMP, CL2P	26 (LBS.) 3126
18	4	STR.	.172	30	C(UL), FT6, CMP, CL2P	33 (LBS.) 3115
18	6	STR.	.212	30	C(UL), FT6, CMP, CL2P	47 (LBS.) 3116+
18	8	STR.	.232	30	C(UL), FT6, CMP, CL2P	61 (LBS.) 3117+
18	10	STR.	.270	30	C(UL), FT6, CMP, CL2P	75 (LBS.) 3118+
18	12	STR.	.277	30	C(UL), FT6, CMP, CL2P	88 (LBS.) 3119+
18	15	STR.	.316	30	C(UL), FT6, CMP, CL2P	109 (LBS.) 3120+•
16	2	STR.	.172	32	C(UL), FT6, CMP, CL2P	28 (LBS.) 3121
16	3	STR.	.186	31	C(UL), FT6, CMP, CL2P	38 (LBS.) 3129+
16	4	STR.	.202	32	C(UL), FT6, CMP, CL2P	50 (LBS.) 3122+
14	2	STR.	.208	34	C(UL), FT6, CMP, CL2P	39 (LBS.) 3123+
14	3	STR.	.220	33	C(UL), FT6, CMP, CL2P	53 (LBS.) 3130
14	4	STR.	.244	34	C(UL), FT6, CMP, CL2P	70 (LBS.) 3124+
12	2	STR.	.265	35	C(UL), FT6, CMP, CL2P	61 (LBS.) 3125+

*Not Twisted

+Spools Only

• Consult factory for availability.