

Description: 22 AWG 4/C STR CMP/CL2P  
Compliance: UL Standards 13 & 444; NEC Articles 725 & 800

#### Construction:

Conductor 22 AWG 7/.0096 Bare Copper  
Insulation Plenum PVC  
Color Blk, Wht, Red, Grn  
Thickness 0.007" nom.  
Diameter 0.043" nom.  
Lay Length Straight

Jacket  
Type PVC Plenum  
Color Natural  
Thickness 0.015" nom.  
Diameter 0.136" nom.  
Legend (Ink Print) HONEYWELL P/N 3104 4C22 3038058 (ETL) CL2P OR CMP C(ETL)US FT6 (RoHS)  
W/O# XXXXXX-XXXXXX XXXXX FT DEVICE/ZONE A B C D E F 1 2 3 4 5 6 7 8 9

#### Properties

Temperature Rating -20 to 60 °C  
Operating Voltage 300 Volts max.  
Capacitance 25 pf/ft nom.  
Impedance 85 Ohms nom.  
DC Resistance 16.5 Ohms/M' at 20°C  
Flame Rating UL 910, NFPA 262, CSA FT6