



POLARIS PRODUCTS

Insulated Multi-Cable Connector Blocks

TYPE: ITG (Insul-Tap for Two Wires)

- Designed for use with fine stranded, flexible, and extra flexible cable.
- Makes motor Lead connections a snap
- Insulated with High Dielectric Strength Plasticsol
- Molded for precise fit and supplied with removable access plugs over the hex screws
- Eliminates the need for cover and taping
- Abrasion and chemical resistant
- Will not support combustion
- Cold Temperature Rated to -45 degrees C



ITOG



ITG

Catalog Number	Number of Ports	Wire Range (Building Wire)	Wire Range (Extra Flexible)	Dimensions, Inches			Hex size
				H	W	L	
ITG #6	2	#6 - #14	#6 - #14	1.31	1.2	1.13	S
ITG #1	2	#1 - #10	#2 - #10	1.71	1.53	1.6	3/16
ITG 3/0	2	3/0 - #4	2/0 - #2	1.81	1.59	1.85	1/4
ITOG #6	2	#6 - #14	#6 - #14	1.31	1.27	1.13	S
ITOG #1	2	#1 - #10	#2 - #10	1.71	1.62	1.6	3/16