

POLARIS™ INSULATED CONNECTORS
Multi-Conductor Connector
One Side Wire Entry
IPL SERIES



FEATURES

- Wire entry ports on one side only.
- Eliminates the need for cover and taping.
- Insulated with high-dielectric strength plastisol.
- Molded for precise fit and supplied with removable access plugs over the hex screws.
- Abrasion and chemical resistant. UV resistant.
- Will not support combustion.

RATINGS



UL Listed 486B Wire Connector.

TEMPERATURE RATING/VOLTAGE:

AL9CU. Cold temperature rated to -45°C, rated 600V, 90°C.

WIRE TYPE:

Dual rated for use with copper and/or aluminum cables. Not recommended for fine-stranded, flexible wire.

All dimensional data is listed in inches.

CAT. NO.	NO. OF PORTS
IPL4-3	3
IPL4-3A	3
IPL4-4	4
IPL4-4A	4
IPL4-5	5
IPL4-6	6
IPL4-8	8
IPL4-8A	8
IPL4-10	10
IPL4-12	12
IPL4-14	14
IPL1/0-3	3
IPL1/0-4	4
IPL1/0-5	5
IPL1/0-6	6
IPL1/0-8	8
IPL1/0-10	10
IPL1/0-12	12
IPL1/0-14	14
IPL3/0-3	3
IPL3/0-4	4
IPL3/0-5	5
IPL3/0-6	6
IPL3/0-8	8